

25kV CU 133% TRXLPE LCT LLDPE

Single Conductor, 320 Mils Tree Retardant Cross Linked Polyethylene, 133% Insulation Level, Longitudinally Corrugated Tape Shield, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
- Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
- Insulation:** 320 Mils Tree Retardant Cross Linked Polyethylene 133% insulation level
- Insulation Shield:** Strippable semi-conducting cross-linked copolymer
- Tape Shield:** 10 mils Longitudinally Corrugated Tape Shield
- Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 25kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Rural Utility Standard RUS 1728F-U1 or 1728.204 (Electric standards and specifications for materials and construction)
- UL 1072 Listed as MV 90 When Specified
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 25000 VOLTS TRXLPE INSULATION 320 MILS -- (NESC) --
SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET



Table 1 – Weights and Measurements

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	mil	inch	lb /1000ft	inch	lb
1 (Solid)	0.289	0.967	320	1.047	80	1.307	884	15.7	669
1 (19)	0.322	1.000	320	1.080	80	1.340	910	16.1	669
1/0 (Solid)	0.324	1.002	320	1.082	80	1.342	979	16.1	844
1/0 (19)	0.361	1.039	320	1.119	80	1.379	1008	16.5	844
2/0 (19)	0.405	1.083	320	1.163	80	1.423	1128	17.1	1064
3/0 (19)	0.456	1.134	320	1.214	80	1.474	1277	17.7	1342
4/0 (19)	0.512	1.190	320	1.270	80	1.530	1457	18.4	1692
250 (37)	0.558	1.244	320	1.324	80	1.584	1620	19.0	2000
350 (37)	0.661	1.347	320	1.427	110	1.747	2116	21.0	2800
500 (37)	0.789	1.475	320	1.555	110	1.875	2688	22.5	4000
750 (61)	0.968	1.664	320	1.744	110	2.064	3631	24.8	6000
1000 (61)	1.117	1.813	320	1.893	110	2.213	4532	26.6	8000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.128	0.162	0.082	0.056	0.101	1.46	0.216 + j0.754	0.162 + j0.054	2956	175	220
1 (19)	0.128	0.162	0.077	0.054	0.108	1.56	0.216 + j0.753	0.162 + j0.055	3048	175	220
1/0 (Solid)	0.102	0.128	0.076	0.054	0.108	1.56	0.182 + j0.750	0.128 + j0.052	3053	200	250
1/0 (19)	0.102	0.128	0.071	0.052	0.116	1.67	0.182 + j0.749	0.128 + j0.053	3156	200	250
2/0 (19)	0.081	0.102	0.066	0.051	0.124	1.79	0.156 + j0.745	0.102 + j0.051	3278	230	285
3/0 (19)	0.064	0.081	0.061	0.049	0.134	1.93	0.135 + j0.741	0.081 + j0.049	3419	260	320
4/0 (19)	0.051	0.065	0.057	0.047	0.145	2.09	0.119 + j0.736	0.065 + j0.047	3574	300	365
250 (37)	0.043	0.056	0.054	0.046	0.152	2.19	0.110 + j0.732	0.056 + j0.046	3724	315	396
350 (37)	0.031	0.041	0.048	0.044	0.172	2.48	0.095 + j0.724	0.041 + j0.044	4009	390	475
500 (37)	0.022	0.030	0.042	0.042	0.195	2.81	0.084 + j0.717	0.030 + j0.042	4364	470	565
750 (61)	0.014	0.023	0.036	0.039	0.226	3.26	0.077 + j0.708	0.023 + j0.039	4888	585	680
1000 (61)	0.011	0.019	0.032	0.037	0.253	3.65	0.073 + j0.701	0.019 + j0.037	5301	670	750

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.



Table 3 – Weights and Measurements (Metric)

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	mm	mm	kg/km	mm	newton
1 (Solid)	7.34	24.56	8.13	26.59	2.03	33.20	1316	398.78	2977
1 (19)	8.18	25.40	8.13	27.43	2.03	34.04	1354	408.94	2977
1/0 (Solid)	8.23	25.45	8.13	27.48	2.03	34.09	1457	408.94	3756
1/0 (19)	9.17	26.39	8.13	28.42	2.03	35.03	1500	419.10	3756
2/0 (19)	10.29	27.51	8.13	29.54	2.03	36.14	1679	434.34	4735
3/0 (19)	11.58	28.80	8.13	30.84	2.03	37.44	1900	449.58	5972
4/0 (19)	13.00	30.23	8.13	32.26	2.03	38.86	2168	467.36	7529
250 (37)	14.17	31.60	8.13	33.63	2.03	40.23	2411	482.60	8900
350 (37)	16.79	34.21	8.13	36.25	2.79	44.37	3149	533.40	12460
500 (37)	20.04	37.47	8.13	39.50	2.79	47.63	4000	571.50	17800
750 (61)	24.59	42.27	8.13	44.30	2.79	52.43	5404	629.92	26700
1000 (61)	28.37	46.05	8.13	48.08	2.79	56.21	6744	675.64	35600

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor



Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1 (Solid)	0.4199	0.53	0.0250	0.1837	0.331	4.7900	0.216 + j0.754	0.162 + j0.054	2956	175	220
1 (19)	0.4199	0.53	0.0235	0.1772	0.354	5.1181	0.216 + j0.753	0.162 + j0.055	3048	175	220
1/0 (Solid)	0.3346	0.42	0.0232	0.1772	0.354	5.1181	0.182 + j0.750	0.128 + j0.052	3053	200	250
1/0 (19)	0.3346	0.42	0.0216	0.1706	0.381	5.4790	0.182 + j0.749	0.128 + j0.053	3156	200	250
2/0 (19)	0.2657	0.33	0.0201	0.1673	0.407	5.8727	0.156 + j0.745	0.102 + j0.051	3278	230	285
3/0 (19)	0.2100	0.27	0.0186	0.1608	0.440	6.3320	0.135 + j0.741	0.081 + j0.049	3419	260	320
4/0 (19)	0.1673	0.21	0.0174	0.1542	0.476	6.8570	0.119 + j0.736	0.065 + j0.047	3574	300	365
250 (37)	0.1411	0.18	0.0165	0.1509	0.499	7.1850	0.110 + j0.732	0.056 + j0.046	3724	315	396
350 (37)	0.1017	0.13	0.0146	0.1444	0.564	8.1365	0.095 + j0.724	0.041 + j0.044	4009	390	475
500 (37)	0.0722	0.10	0.0128	0.1378	0.640	9.2192	0.084 + j0.717	0.030 + j0.042	4364	470	565
750 (61)	0.0459	0.08	0.0110	0.1280	0.741	10.6955	0.077 + j0.708	0.023 + j0.039	4888	585	680
1000 (61)	0.0361	0.06	0.0098	0.1214	0.830	11.9751	0.073 + j0.701	0.019 + j0.037	5301	670	750

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

