



46kV CU 100% TRXLPE One-Third Neutral LLDPE

Single Conductor, 445 Mils Tree Retardant Cross Linked Polyethylene, 100% Insulation Level, One-third Concentric Neutral, Linear Low Density Polyethylene (LLDPE) Jacket. Silicone Free



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Moisture blocked class B compressed stranded soft drawn bare copper per ASTM B3 and ASTM B8 (Conductor moisture block optional and tinned copper per ASTM B33 optional)
2. **Conductor Shield:** Conventional Semi-conducting cross-linked copolymer; Supersmooth conductor shield optional; A conductor tape is used for cable size larger than or equal to 1500 Kcmil
3. **Insulation:** 445 Mils Tree Retardant Cross Linked Polyethylene 100% insulation level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Concentric Neutral:** Helically applied soft drawn bare copper one-third concentric neutral
6. **Overall Jacket:** Linear Low Density Polyethylene (LLDPE) Jacket, black with red extruded stripes; PowerGlide® LLDPE jacket optional

APPLICATIONS AND FEATURES:

Southwire's 46kV cables are suited for use in wet and dry areas, conduits, ducts, direct burial, sunlight, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation. 130°C for emergency overload, and 250°C for short circuit conditions. Jacket types available that can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Optional CSA 68.5: -40°C and MV 90°C optional marking available upon request

SAMPLE PRINT LEGEND:

SOUTHWIRE HI-DRI(R) [CONDUCTOR SIZE] [AWG or KCMIL] CU 46000 VOLTS TRXLPE INSULATION 445 MILS -- (NESC) -- SOUTHWIRE {MMM} {YYYY} NON-CONDUCTING JACKET





Table 1 – Weights and Measurements

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
4/0 (19)	0.512	1.440	445	1.550	18x14	0.146	75	1.828	2029	14.6	1692
250 (37)	0.558	1.494	445	1.604	21x14	0.125	75	1.882	2245	15.1	2000
350 (37)	0.661	1.597	445	1.737	29x14	0.090	75	2.015	2813	16.1	2800
500 (37)	0.789	1.725	445	1.865	26x12	0.063	75	2.177	3560	17.4	4000
750 (61)	0.968	1.914	445	2.054	25x10	0.041	75	2.408	4831	19.3	6000
1000 (61)	1.117	2.063	445	2.223	33x10	0.031	75	2.577	6062	20.6	8000

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance	Positive Sequence Impedance	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
4/0 (19)	0.051	0.065	0.065	0.051	0.405	3.2	0.119 + j0.727	0.065 + j0.052	6277	300
250 (37)	0.043	0.056	0.061	0.050	0.430	3.4	0.110 + j0.724	0.056 + j0.050	7323	
350 (37)	0.031	0.041	0.055	0.047	0.478	3.8	0.095 + j0.717	0.041 + j0.048	10113	400
500 (37)	0.022	0.030	0.049	0.045	0.537	4.3	0.084 + j0.710	0.030 + j0.046	14406	470
750 (61)	0.014	0.023	0.042	0.043	0.623	5.0	0.077 + j0.700	0.023 + j0.043	22019	560
1000 (61)	0.011	0.019	0.038	0.041	0.691	5.5	0.073 + j0.694	0.019 + j0.041	29065	

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.





Table 3 – Weights and Measurements (Metric)

Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
AWG/ Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
4/0 (19)	13.00	36.58	11.30	39.37	18x14	0.48	1.91	46.43	3019	370.84	7529
250 (37)	14.17	37.95	11.30	40.74	21x14	0.41	1.91	47.80	3341	383.54	8900
350 (37)	16.79	40.56	11.30	44.12	29x14	0.30	1.91	51.18	4186	408.94	12460
500 (37)	20.04	43.82	11.30	47.37	26x12	0.21	1.91	55.30	5298	441.96	17800
750 (61)	24.59	48.62	11.30	52.17	25x10	0.13	1.91	61.16	7189	490.22	26700
1000 (61)	28.37	52.40	11.30	56.46	33x10	0.10	1.91	65.46	9021	523.24	35600

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C
AWG/ Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp
4/0 (19)	0.1673	0.21	0.0198	0.1673	1.329	10.4987	0.119 + j0.727	0.065 + j0.052	6277	300
250 (37)	0.1411	0.18	0.0186	0.1640	1.411	11.1549	0.110 + j0.724	0.056 + j0.050	7323	
350 (37)	0.1017	0.13	0.0168	0.1542	1.568	12.4672	0.095 + j0.717	0.041 + j0.048	10113	400
500 (37)	0.0722	0.10	0.0149	0.1476	1.762	14.1076	0.084 + j0.710	0.030 + j0.046	14406	470
750 (61)	0.0459	0.08	0.0128	0.1411	2.044	16.4042	0.077 + j0.700	0.023 + j0.043	22019	560
1000 (61)	0.0361	0.06	0.0116	0.1345	2.267	18.0446	0.073 + j0.694	0.019 + j0.041	29065	

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft, Spacing: one diameter spacing center-to-center.

CN
Calculator

