

# CU Compact 5/8kV NLEPR Insulation 133/100% IL SIM-PVC Jacket. MV 105 - Tray Rated - Sunlight Resistant - For Direct Burial

Type MV-105 Single Conductor Compact Copper, 5kV/8kV 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133%/100% Insulation Level, Tape Shield, SIMpull<sup>®</sup> Polyvinyl Chloride (PVC) Jacket, Dual Rated UL/CSA



Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Class B compact stranded per ASTM B496
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 115 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Overall Jacket:** Polyvinyl Chloride (PVC)

## APPLICATIONS AND FEATURES:

Southwire's 5KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial when installed with a grounding conductor in close proximity that conforms to NEC section 311.36 and 250.4(A)(5), and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend when UL listed. Rated at -25°C for cold bend and cold impact and marked with "LTDD" when CSA listed or dual UL/CSA listed. ST1 (low smoke) Rated for sizes 1/0 and larger. PVC jacket is made with SIM technology and has a coefficient of friction COF of 0.2. Cable can be installed in conduit without the aid of lubrication. Rated for 1000 lbs./FT maximum sidewall pressure.

## SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B496 Compact Round Concentric-lay-standard copper
- UL 1072 Medium-Voltage Power Cables
- UL 1685 FT4-ST1 Vertical-Tray Fire Propagation and Smoke Release Test (1/0 and Larger)
- CSA C22.2 No.230 Tray Cables - Rated TC-ER (1/0 AWG and Larger)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- CSA C68.10 Shielded Power Cables for Commercial and Industrial Applications - 5 to 46 KV
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- ICEA S-97-682 Standard for Shielded Utility Cable Rated for 5 - 46kV
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test (1/0 and Larger)
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

### SAMPLE PRINT LEGEND:

{SQFTG\_DUAL} SOUTHWIRE SIMpull{R} POWER CABLE MASTER-DESIGN {UL} XXX KCMIL CPT CU 115 MILS NL-EPR 5KV 133%/8KV 100% INS LEVEL 25%TS MV-105 FOR CT USE ST1 SUN RES (NESC) -- {CSA} XXX KCMIL CPT CU 2.92mm (115 mils) NL-EPR 5KV 133%/8KV 100% INS LEVEL 25%TS SR TC-ER 105{D}C FT4 -25{D}C LTDD -- PAT www.patentSW.com -- RoHS

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Strand Count	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Jacket Thickness	Approx. OD	Approx. Weight	Max Pull Tension	Min Bending Radius	Conduit Size*
	AWG/ Kcmil	No. of Strands	inch	inch	inch	mil	inch	lb/1000ft	lb	inch	inch
TBA	2	7	0.268	0.536	0.596	55	0.726	403	530	8.7	2.0
TBA	1	19	0.298	0.566	0.626	55	0.756	468	669	9.0	2.5
TBA	1/0	19	0.336	0.604	0.664	55	0.794	551	844	9.5	2.5
TBA	2/0	19	0.376	0.644	0.704	80	0.884	694	1064	10.6	2.5
TBA	3/0	19	0.422	0.690	0.750	80	0.930	821	1342	11.1	3.0
TBA	4/0	19	0.474	0.742	0.802	80	0.982	980	1692	11.7	3.0
TBA	250	37	0.520	0.796	0.856	80	1.036	1126	2000	12.4	3.0
TBA	350	37	0.615	0.891	0.951	80	1.131	1477	2800	13.5	3.5
TBA	500	37	0.735	1.011	1.071	80	1.251	1993	4000	15.0	3.5
679723	750	61	0.908	1.194	1.254	80	1.434	2922	6000	17.2	4.0
TBA	1000	61	1.060	1.346	1.406	80	1.586	3696	8000	19.0	4.5

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM



**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C	Allowable Ampacity In Air 90/105°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ/1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.036	0.045	0.568 + j0.521	0.204 + j0.044	1877	145/155	190/215
1	0.128	0.162	0.033	0.043	0.529 + j0.503	0.162 + j0.042	1970	170/180	225/250
1/0	0.102	0.128	0.030	0.041	0.498 + j0.482	0.128 + j0.04	2088	195/210	260/290
2/0	0.081	0.102	0.028	0.041	0.472 + j0.46	0.102 + j0.04	2212	220/235	300/330
3/0	0.064	0.081	0.025	0.040	0.452 + j0.437	0.081 + j0.038	2354	250/270	345/385
4/0	0.051	0.065	0.023	0.038	0.436 + j0.413	0.065 + j0.037	2515	290/310	400/445
250	0.043	0.056	0.022	0.038	0.426 + j0.39	0.056 + j0.036	2683	320/345	445/495
350	0.031	0.041	0.019	0.036	0.406 + j0.352	0.042 + j0.034	2977	385/415	550/615
500	0.022	0.030	0.016	0.034	0.387 + j0.312	0.031 + j0.032	3349	470/505	695/775
750	0.014	0.023	0.014	0.032	0.364 + j0.261	0.024 + j0.031	3916	585/630	900/1000
1000	0.011	0.019	0.012	0.031	0.345 + j0.227	0.02 + j0.03	4387	670/720	1075/1200

\* Ampacities are based on:

\* For Duct: Table 310.60(C)(77) Detail 1.

\* For Free Air: Table 310.60(C)(69).

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

\* Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

\* Capacitive Reactance is between Phase-to-Shield.

