

## 3/C CU 15kV 220 NLEPR 133% GSIA PVC MV-105

Type MV-105 Three Conductor Copper, 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level, Tape Shield, Galvanized Steel Interlocked Armor (GSIA), Polyvinyl Chloride (PVC) Jacket. Silicone Free




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** 220 Mils No Lead Ethylene Propylene Rubber (NL-EPR) 133% Insulation Level,
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductor:** Class B compressed stranded bare copper ground per ASTM B3 and ASTM B8 (Tinned Copper per ASTM B33 optional)
7. **Filler:** Wax paper filler
8. **Binder:** Polypropylene tape
9. **Armor:** Galvanized Steel Interlocked Armor (GSIA)
10. **Overall Jacket:** Polyvinyl Chloride (PVC)

### APPLICATIONS AND FEATURES:

Southwire's 15KV cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 105°C for normal operation, 140°C for emergency overload, and 250°C for short circuit conditions. Rated at -35°C for cold bend. For uses in Class I and II, Division 2 hazardous locations per NEC Article 501 and 502. Rated for 1000 lbs./FT maximum sidewall pressure.

### SPECIFICATIONS:

- ASTM B3 Standard Specification for Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 1072 Medium-Voltage Power Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-93-639 (NEMA WC 74) 5-46 KV Shielded Power Cable
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

**SAMPLE PRINT LEGEND:**

{SQFTG\_DUAL} SOUTHWIRE{R} POWER CABLE MASTER-DESIGN {UL} 3/C X AWG CU 220 MILS NL-EPR 15KV 133% INS LEVEL 25%TS GW 1 X X AWG CU MV-105 FOR CT USE SUN. RES. FOR DIRECT BURIAL {NESC}

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Diameter Over Insulation Shield	Ground	Jacket Thickness <sup>1</sup>	Approx. OD	Approx. Weight	Max Pull Tension	Min Bending Radius
	AWG/ Kcmil	inch	inch	inch	No. x AWG	mil	inch	lb/1000ft	lb	inch
610105	2	0.282	0.755	0.815	1 x 6	60	2.254	2951	1592	15.7
TBA	1	0.322	0.8	0.86	1 x 4	60	2.342	3437	2008	16.3
TBA	1/0	0.361	0.839	0.899	1 x 4	75	2.457	3848	2534	17.1
TBA	2/0	0.405	0.883	0.943	1 x 4	75	2.552	4263	3194	17.8
581972	2/0	0.405	0.884	0.944	1 x 1	75	2.566	4213	3194	17.9
TBA	3/0	0.456	0.934	0.994	1 x 3	75	2.662	4805	4027	18.6
TBA	4/0	0.512	0.99	1.05	1 x 3	75	2.783	5414	5078	19.4
560801	250	0.558	1.028	1.088	1 x 2	75	3.097	6317	6000	21.6
611038	350	0.661	1.127	1.187	1 x 2	75	3.091	7056	8400	21.6
581973	500	0.789	1.252	1.312	1 x 1	90	3.383	9059	12000	23.6
670992	500	0.789	1.252	1.312	1 x 1/0	90	3.383	9127	12000	23.6
TBA	750	0.968	1.464	1.524	1 x 1/0	90	3.837	12544	18000	26.8

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Zero Sequence Impedance*	Positive Sequence Impedance*	Shield Short Circuit Current 6 Cycles	Allowable Ampacity In Duct 90/105°C <sup>†</sup>	Allowable Ampacity In Air 90/105°C <sup>‡</sup>
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
2	0.162	0.204	0.0523	0.0467	0.576 + j0.452	0.204 + j0.048	2352	150/160	165/185
1	0.128	0.162	0.0483	0.0447	0.534 + j0.432	0.162 + j0.045	2466	170/185	185/210
1/0	0.102	0.128	0.0447	0.043	0.5 + j0.415	0.128 + j0.043	2578	195/210	215/240
2/0	0.081	0.102	0.0416	0.0415	0.472 + j0.397	0.102 + j0.042	2704	220/235	245/275
2/0	0.081	0.102	0.0416	0.0415	0.472 + j0.397	0.102 + j0.042	2704	220/235	245/275
3/0	0.064	0.081	0.0384	0.04	0.449 + j0.377	0.081 + j0.04	2851	250/270	285/315
4/0	0.051	0.065	0.0354	0.0386	0.43 + j0.357	0.065 + j0.039	3011	285/305	325/360
250	0.043	0.056	0.0337	0.0377	0.418 + j0.339	0.056 + j0.038	3166	310/335	360/400
350	0.031	0.041	0.0299	0.0358	0.395 + j0.308	0.041 + j0.036	3462	375/400	435/490
500	0.022	0.03	0.0263	0.0341	0.373 + j0.274	0.03 + j0.034	3829	450/485	535/600
500	0.022	0.03	0.0263	0.0341	0.373 + j0.274	0.03 + j0.034	3829	450/485	535/600
750	0.014	0.023	0.0229	0.0324	0.349 + j0.233	0.024 + j0.032	4371	545/585	670/745

\* Calculations are based on 5 mil 25 % over lapping copper tape shield / Conductor temperature of 90°C / Shield temperature of 45°C / Earth resistivity of 100 ohms-meter

† Ampacities are based on TABLE 310.60(C)(83) of the 2020 National Electrical Code (20°C Ambient Earth Temperature, Thermal Resistance ROH of 90)

‡ Ampacities are based on TABLE 310.60(C)(71) of the 2020 National Electrical Code (40°C Ambient Air Temperature)



**Southwire**



Services