

## 3/C CU 5KV 100% & 133% EPR/CPE RHINOPOWER™ Type MP-GC. MSHA Approved

Class B Cu Conductors, Ethylene Propylene Rubber (EPR) 100% & 133% Insulation Level, Cu Tape Shield, Chlorinated Polyethylene (CPE) Jacket w/ Optional Reflective Stripes, 90°C



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class B compact stranded bare copper per ASTM B3 and ASTM B496
2. **Conductor Shield:** Semi-conducting cross-linked copolymer
3. **Insulation:** Ethylene Propylene Rubber (EPR) 100% and 133% Insulation Level
4. **Insulation Shield:** Strippable semi-conducting cross-linked copolymer
5. **Copper Tape Shield:** Helically wrapped 5 mil copper tape with 25% overlap
6. **Grounding Conductors:** Two Class B compressed stranded bare copper per ASTM B3 and ASTM B8
7. **Ground Check:** Class B compressed stranded bare copper per ASTM B3 and ASTM B8 with yellow high strength, polypropylene insulation
8. **Filler:** Rubber Fillers as needed
9. **Reinforcement:** Tape and Reinforcing twine applied over the core for improved mechanical integrity and ease of stripping
10. **Jacket:** Black, mold cured, single layer, flame resistant, thermosetting Chlorinated Polyethylene (CPE). Alternate jacket colors available
11. **Reflective Stripe:** Highly visible reflective stripe embedded into the outer jacket to increase safety and help prevent cable runover (optional, contact your sales representative for part number)

### APPLICATIONS AND FEATURES:

RHINOPOWER™ Type MP-GC mine power feeder cable is a heavy-duty power cable for use in stationary horizontal HV mine power distribution circuits, for permanent or semi-portable applications with power transmission in deep mines, surface mines, open pits, tunnels, in conduit or duct (not to exceed max rated voltage), and suitable for direct burial in wet or dry locations. For vertical drop requirements consult with factory application specialist.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B496 Compact Round Concentric-lay-standard copper
- ICEA S-75-381 Portable and Power Feeder Cables for Use in Mines
- MSHA Approved



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)

Copyright © 2024 Southwire Company, LLC. All Rights Reserved



Southwire

**CABLETECH  
SUPPORT™**

Services

UPDATED: Jan. 22, 2024, 10:22 p.m. UTC REVISION: 1.000.001

**SAMPLE PRINT LEGEND:**

SOUTHWIRE (R) RHINO™ BRAND CABLE # AWG 3/C COMPACT CU TYPE MP-GC 5000V 100% OR 133% INS. LEVEL P-07-K140017 MSHA

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Diameter Over Insulation	Ground	Ground Check Size	Jacket Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	No.	inch	mil	inch	No. x AWG	AWG	mil	inch	lb/1000ft
578410	2/0	3	19	0.376	90	0.583	2 x 3	8	110	1.740	2664
586912	3/0	3	19	0.422	90	0.653	2 x 2	8	140	1.880	3188
587013	250	2	37	0.520	90	0.759	2 x 1/0	8	140	2.290	4778

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance	Inductive Reactance	Working Tension	Min Bending Radius	Allowable Ampacity In Air 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	lb	inch	Amp
2/0	0.081	0.102	0.022	0.032	910	20.8	243
3/0	0.064	0.081	0.022	0.032	1147	22.5	279
250	0.043	0.056	0.019	0.030	1710	27.4	355

\* Ampacities based upon ICEA S-75-381 Table I-1.

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

