

## Armorlite® Type AC THHN/THWN Circuit Size Copper Conductor

14 AWG through 10 AWG THHN/THWN Insulated Singles Wrapped in Moisture-Resistant, Flame-Retardant Paper. 16 AWG Aluminum Bond Wire. UL Listed. 600 Volts. Rated VW-1. Lightweight Aluminum Interlocked Armor.




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Solid copper per ASTM B3
2. **Insulation:** All phases are insulated with Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Paper Covering:** Moisture-resistant, flame-retardant paper covering
4. **Bond Wire:** Solid #16 AWG aluminum
5. **Armor:** Aluminum Interlocked Armor

### APPLICATIONS AND FEATURES:

**Southwire Armorlite® Type AC Cable is suitable for use as follows:**

- Branch and service power distribution in commercial, industrial, institutional, and multi-residential buildings.
- Fished or embedded in plaster.
- Concealed or exposed installations.
- Dry locations only.
- Environmental air-handling spaces per NEC 300.22 (C).
- Installation in cable tray and approved raceways.
- Under raised floors for information technology equipment conductors and cables per NEC Article 645
- Conductors are individually wrapped with a moisture-resistant, flame-retardant paper covering
- Type THHN/THWN rated 90°C Dry.
- Anti-Short bushing are required

**Southwire Armorlite® Type AC Cable - meets or exceeds the following requirements:**

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) ( [www.ul.com](http://www.ul.com) )
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 320
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- UL 83 Thermoplastic Insulated Wires and Cables
- UL 4 Armored Cables
- REACH/RoHS-2 (Chemical Limit) Compliant



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)



Southwire

**CABLETECH  
SUPPORT™**

Services

- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify “Made in the USA Only!” when ordering to ensure your project receives American made products.

### SAMPLE PRINT LEGEND:

TYPE AC-THH AL ARMOR COPPER THHN CONDUCTORS W/ ALUMINUM BOND WIRE MAXIMUM VOLTS 600V, FOR USE IN CABLE TRAYS-90(D) C - DRY LOCATIONS GAS. & OIL REST.COND.( AL.BOND WIRE)-NOT FOR USE ON DC CIRCUITS

\*CAUTION:NOT TO BE USED WITH SETSCREW CONNECTOR

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Conductor Number	Color	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Diameter Over Armor	Overall Weight
	AWG/ Kcmil			inch		mils	inch	lbs/1000ft
610293◇	14	2	BK/WE	0.064	Solid	20	0.468	89
610294◇	14	3	BK/RD/WE	0.064	Solid	20	0.488	108
610296◇	14	4	BK/RD/BE/ WE	0.064	Solid	20	0.520	129
610231◇	12	2	BK/WE	0.080	Solid	20	0.501	109
553270◇	12	2	BN/GY	0.080	Solid	20	0.501	109
610232◇	12	3	BK/RD/WE	0.080	Solid	20	0.524	137
553276◇	12	3	BN/GY/OE	0.080	Solid	20	0.524	138
610297◇	12	4	BK/RD/BE/ WE	0.080	Solid	20	0.560	167
610298◇	10	2	BK/WE	0.101	Solid	25	0.555	141
610299◇	10	3	BK/RD/WE	0.101	Solid	25	0.583	182
610300◇	10	4	BK/RD/BE/ WE	0.101	Solid	25	0.626	224

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 60°C	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
14	2	3.2	2.631	3.170	0.033	15	20	25
14	3	3.4	2.631	3.170	0.033	15	20	25
14	4	3.6	2.631	3.170	0.041	12	16	20
12	2	3.5	1.662	2.002	0.031	20	25	30
12	2	3.5	1.662	2.002	0.031	20	25	30
12	3	3.6	1.662	2.002	0.031	20	25	30
12	3	3.6	1.662	2.002	0.031	20	25	30
12	4	3.9	1.662	2.002	0.039	16	20	24
10	2	3.8	1.040	1.253	0.030	30	35	40
10	3	4.0	1.040	1.253	0.030	30	35	40
10	4	4.3	1.040	1.253	0.038	24	28	32



\* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

\* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

