

35kV AL 100% TRXLPE One-Third (Based on Short Circuit) Primary UD HI-DRI-PLUS® Renewable (Solar or Wind)

Moisture Blocked Aluminum Conductors. TRXLPE Insulation. One-Third Concentric Neutrals. XLPE Jacket




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Moisture Blocked 1350 H16/H26 Aluminum, Class B Compressed or Compressed Unilay Stranded
- Strand Shield:** Semi-conducting Crosslinked Polyethylene
- Insulation:** Tree Retardant Crosslinked Polyethylene (TRXLPE)
- Insulation Shield:** Strippable Semi-conducting Crosslinked Polyethylene
- Concentric Neutral:** Annealed Copper Wires Helically Applied One-Third Concentric Neutral
- Overall Jacket & Water Block:** HI-DRI-PLUS® Water Swellable Powder Black Crosslinked Polyethylene (XLPE) with Red Extruded Stripes

APPLICATIONS AND FEATURES:

- Predominately used for renewable projects with wind or solar applications.
- Suitable for use in wet or dry locations, direct burial, underground ducts, and exposure to direct sunlight.
- To be used at conductor temperature not to exceed 105°C normal operation.
- UL listed MV-105
- Under short circuit conditions, the maximum allowable shield temperature for crosslinked jackets is 350°C as opposed to only 200°C for a PE type of jacket. The higher temperature allows for more fault current capacity, thus reducing the amount of copper required in the neutral design.
- Not recommended for use above 90°C in wind farm applications

SPECIFICATIONS:

- UL 1072 Medium-Voltage Power Cables
- ICEA S-94-649 Standard for Concentric Neutral Cables Rated 5 - 46kV
- AEIC CS-8 Specification for extruded dielectric shielded power cables rated for 5 through 46KV (Qualification Test Requirements)
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



CN Calculator



Southwire

**CABLETECH
SUPPORT™**

Services

SAMPLE PRINT LEGEND:

SOUTHWIRE(R) (UL) HI-DRI-PLUS(R) AWG XX AL 35000 VOLTS TR XLPE INSULATION XX MILS (NESC) MV105 -- SOUTHWIRE (MM/YYYY) NON-CONDUCTING JACKET (PLANT) SEQUENTIAL FOOTAGE MARKS

Table 1 – Weights and Measurements

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/ Kcmil	inch	inch	mil	inch	No. x AWG	Ω /1000ft	mil	inch	lb / 1000ft	inch	lb
TBA	1/0 (19)	0.361	1.089	345	1.199	6x14	0.438	50	1.427	846	11.4	633
TBA	3/0 (19)	0.443	1.171	345	1.281	9x14	0.292	50	1.509	1007	12.1	1006
TBA	250 (37)	0.558	1.294	345	1.404	13x14	0.202	75	1.682	1317	13.5	1500
662829 [^]	750 (61)	0.968	1.708	345	1.848	24x12	0.069	75	2.163	2441	17.3	4500
662818 [^]	1000 (61)	1.117	1.857	345	1.997	20x10	0.052	75	2.354	3021	18.8	6000
662816 [^]	1250 (61)	1.250	2.000	345	2.140	25x10	0.041	75	2.497	3534	20.0	7500
663836	1250 (61)	1.250	2.000	345	2.140	25x10	0.041	75	2.497	3534	20.0	7500

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

[^] Non-UL listed

Table 2 – Electrical and Engineering Data

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/ Kcmil	Ω/1000ft	Ω/1000ft	MΩ*1000ft	Ω/1000ft	A/1000ft	W/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0 (19)	0.167	0.211	0.074	0.053	0.155	3.13	0.265 + j0.747	0.211 + j0.054	3103	160	195
3/0 (19)	0.105	0.132	0.066	0.050	0.176	3.55	0.186 + j0.740	0.132 + j0.050	4655	210	250
250 (37)	0.071	0.090	0.057	0.047	0.204	4.12	0.144 + j0.73	0.090 + j0.047	6724	257	302
750 (61)	0.024	0.033	0.038	0.040	0.300	6.06	0.087 + j0.705	0.033 + j0.040	19725	470	530
1000 (61)	0.018	0.026	0.034	0.039	0.335	6.76	0.080 + j0.698	0.026 + j0.039	26129	530	585
1250 (61)	0.014	0.023	0.031	0.038	0.365	7.37	0.077 + j0.437	0.023 - j0.218	32661		
1250 (61)	0.014	0.023	0.031	0.038	0.365	7.37	0.077 + j0.437	0.023 - j0.218	32661		



Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | www.southwire.com



CN Calculator



Southwire

**CABLETECH
SUPPORT™**

Services

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Diameter Over Conductor	Diameter Over Insulation	Insul. Thickness	Diameter Over Insulation Shield	Concentric Neutral	Neutral DC Resistance 25°C	Jacket Thickness	Approx. OD	Approx. Weight	Min Bending Radius	Max Pull Tension
	AWG/Kcmil	mm	mm	mm	mm	No. x AWG	Ω/km	mm	mm	kg/km	mm	newton
TBA	1/0 (19)	9.17	27.66	8.76	30.45	6x14	1.44	1.27	36.25	1259	289.56	2817
TBA	3/0 (19)	11.25	29.74	8.76	32.54	9x14	0.96	1.27	38.33	1499	307.34	4477
TBA	250 (37)	14.17	32.87	8.76	35.66	13x14	0.66	1.91	42.72	1960	342.90	6675
662829 [^]	750 (61)	24.59	43.38	8.76	46.94	24x12	0.23	1.91	54.94	3633	439.42	20025
662818 [^]	1000 (61)	28.37	47.17	8.76	50.72	20x10	0.17	1.91	59.79	4496	477.52	26700
662816 [^]	1250 (61)	31.75	50.80	8.76	54.36	25x10	0.13	1.91	63.42	5259	508.00	33375
663836	1250 (61)	31.75	50.80	8.76	54.36	25x10	0.13	1.91	63.42	5259	508.00	33375

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Pulling tension based on pulling eye directly connected to conductor

[^] Non-UL listed

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Capacitive Reactance @ 60Hz	Inductive Reactance @ 60Hz	Charging Current	Dielectric Loss	Zero Sequence Impedance*	Positive Sequence Impedance*	Short Circuit Current @ 30 Cycle	Allowable Ampacity in Duct 90°C	Allowable Ampacity Directly Buried 90°C
AWG/Kcmil	Ω/km	Ω/km	MΩ*km	Ω/km	A/km	W/km	Ω/1000ft	Ω/1000ft	Amp	Amp	Amp
1/0 (19)	0.5479	0.69	0.0226	0.1739	0.509	10.2690	0.265 + j0.747	0.211 + j0.054	3103	160	195
3/0 (19)	0.3445	0.43	0.0201	0.1640	0.577	11.6470	0.186 + j0.740	0.132 + j0.050	4655	210	250
250 (37)	0.2329	0.30	0.0174	0.1542	0.669	13.5171	0.144 + j0.73	0.090 + j0.047	6724	257	302
750 (61)	0.0787	0.11	0.0116	0.1312	0.984	19.8819	0.087 + j0.705	0.033 + j0.040	19725	470	530
1000 (61)	0.0591	0.09	0.0104	0.1280	1.099	22.1785	0.080 + j0.698	0.026 + j0.039	26129	530	585
1250 (61)	0.0459	0.08	0.0094	0.1247	1.198	24.1798	0.077 + j0.437	0.023 - j0.218	32661		
1250 (61)	0.0459	0.08	0.0094	0.1247	1.198	24.1798	0.077 + j0.437	0.023 - j0.218	32661		

*Ampacities for Direct Buried are based on ICEA P-117-734-2016 Single-Conductor Solid Dielectric 15-35kV. Single Circuit Flat Direct Buried Figure 3

*Ampacities for Duct are based on ICEA P-117-734-2016 for Single-Conductor Solid Dielectric 15-35kV. Single Circuit Trefoil Conduit Figure 7.

*Sequence Impedance values are based on Rho Earth Resistivity: 100 Ohm-Meter/1000ft.

