



**Royal® EXCELENE® NON-UL WELDING CABLE. Silicone Free**

600 Volt 105°C Flexible Cord. Heat, Abrasion, Tear Resistant, Moisture and Flexible EPDM Jacket.




Image not to scale. See Table 1 for dimensions.

**CONSTRUCTION:**

- 1. Conductor:** Annealed flexible soft drawn bare copper per ASTM B3.
- 2. Separator:** Paper separator for ease of stripability
- 3. Insulation:** EPDM, Black (Other colors available upon request)

**APPLICATIONS AND FEATURES:**

Southwire Excelene® Welding cable, extra flexible, rated for -50°C to 105°C temperatures. This cable used for secondary voltage resistance welding cable leads, National electrical code Article 630 electric welders and for temporary power industrial applications.

**SPECIFICATIONS:**

- RoHS Compliant Lead-Free, Silicone-Free

**SAMPLE PRINT LEGEND:**

SOUTHWIRE® ROYAL® EXCELENE® XXX KCMIL (XXXmm<sup>2</sup>) WELDING CABLE 600V -50C TO +105C MADE IN USA--  
Sequential Footage Marking--

**PACKAGING:**

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Cond. Strands No.	Jacket Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft	Ampacity Amp	Insul. Color
104150	1/0	1	1026	85	0.525	411	260	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Ampacities are based on TABLE 400.5(A)(2) of the 2023 National Electrical Code and CEC Table 12(A). The ampacity values assume a continuous sinusoidal 60 Hz current and are for reference only and should not be used as a final value.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Cond. Strands No.	Jacket Thickness mm	Approx. OD mm	Approx. Weight kg/km	Ampacity * Amp	Insul. Color
104150	1/0	1	1026	2.16	13.33	612	260	BK

