



## TCU 600V XLPE Insulation Thermoplastic CPE-TP Jacket XHHW-2 Table 1 Color Code. CT Rated - Sunlight Resistant - For Direct Burial - Silicone Free

Type TC-ER Control Cable 600 Volt Tinned Copper Conductors, Ethylene Propylene Rubber (EPR) Insulation XHHW-2 Thermoplastic Chlorinated Polyethylene (CPE-TP) Jacket with 1 Tinned Copper Ground, Control Cable Conductor Identification Method 1 Table 2. VW-1 rated




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** 7 strands class B compressed tinned copper per ASTM B33 and ASTM B8
2. **Insulation:** Ethylene Propylene Rubber (EPR) XHHW-2, 30 Mil's thick for all cable sizes
3. **Grounding Conductor:** Class B compressed stranded tinned copper per ASTM B33 and ASTM B8
4. **Overall Jacket:** Thermoplastic Chlorinated Polyethylene (CPE-TP) Jacket

### APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type TC-ER control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, and 250°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10.

### SPECIFICATIONS:

- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- UL 44 Thermoset-Insulated Wires and Cables
- UL 44 VW-1 Vertical flame test on individual conductors
- UL 1277 Electrical Power and Control Tray Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- ICEA S-58-679 Control Cable Conductor Identification Method 1 Table 2
- ICEA S-73-532 Standard for Control, Thermocouple Extension and Instrumentation Cables
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test





**SAMPLE PRINT LEGEND:**

{SQFTG} SOUTHWIRE® XX AWG (X.XX{mm<sup>2</sup>}) 3/C W/GRND EPR/CPE TYPE TC-ER XHHW-2 CDRS GW 1 X XX AWG  
TINNED E75755 {UL} 600V 90°C DRY/90°C WET OIL RES I SUNLIGHT RESISTANT DIRECT BURIAL FT4/IEEE 1202 -- {NOM}-  
ANCE EPR/CPE Tipo XHHW-2 SR FT4 600V 90°C USA





**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity 75°C	Allowable Ampacity 90°C	Jacket Color
	AWG	No.	strands	mil	No. x AWG	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft	inch	Amp	Amp	
12 AWG																
591961◇	12	3	7	30	1 x 12	45	0.450	81	143	1.662	2.002	0.054	1.8	25	30	Black

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

† Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

‡ Ampacities have been adjusted for more than Three Current-Carrying Conductors.

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

