



# Transformer Riser Wire, Protected Ground Wire (PGW), Cathodic Protection (CP) Cables, LLDPE

Black Polyethylene Covered. Solid or Stranded Soft Drawn Copper Conductor




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Conductors are solid or stranded compressed copper
- Covering:** Black Linear Low Density Polyethylene (LLDPE) also known as High Molecular Weight Polyethylene (HMWPE)

## APPLICATIONS AND FEATURES:

Used as covered grounding conductors, protected ground wires (PGW), cathodic protection (CP) cables, or on transformers as connection between line conductor and transformer primary bushing in applications where protection from momentary contact from wildlife is needed. Although not treated as an insulation, the thermoplastic polyethylene covering does provide an increased level of protection from momentary grounded contacts caused by wildlife, excessive wind and tree limbs or other grounded objects in the proximity of the high voltage lead. May be used on distribution system voltages up to 35kV line-to-line.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ICEA S-70-547 Weather Resistant Polyethylene Covers Conductors

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Strands	Diameter Over Conductor	Inner Layer Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	#	inch	mil	inch	lb/1000ft
207076	8	7	0.142	110	0.362	87

All dimensions are nominal and subject to normal manufacturing tolerances

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.