

AL XLPE Type RPVU90 2KV

Single Aluminum Conductors, 1000V/2000V, 90°C MAX - 40°C MIN, Sunlight Resistant and FT4 Flame Test Rated



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** AlumaFlex® Compact Stranded Aluminum Alloy (AA-8176)
- Insulation:** Cross Linked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Single aluminum conductor with low temperature, moisture resisting XLPE (cross linked polyethylene) insulation. Sunlight Resistant. This product meets the current RoHS requirements. No lead is added or used in manufacturing.

SPECIFICATIONS:

- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- RoHS Compliant Lead-Free, Silicone-Free
- AA 8176 Stranded Aluminum Alloy Conductors
- CSA Standard C22.2 No. 271 Photovoltaic Cables

SAMPLE PRINT LEGEND:

{SQMTR} SOUTHWIRE LL90458 {CSA} XXX KCMIL (XX{mm²}) COMPACT AL. --- {ALUMAFLEX}® AA8176 RPVU90 1000V/2000V XLPE FT1 (-40°C) SR DIR BUR RoHS

Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Cond. Number | Strand | Insul. Thickness | Insulation Color | Approx. OD | Approx. Weight | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance @ 60Hz | Allowable Ampacity In Raceway 90°C† |
|--------------|------------|--------------|--------|------------------|------------------|------------|----------------|--------------------|------------------|----------------------|----------------------|----------------------------|-------------------------------------|
| | AWG/Kcmil | | No. | mil | | inch | lb/1000ft | inch | lb | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp |
| 669288 | 750 | 1 | 53 | 125 | BK | 1.170 | 947 | 5.8 | 4500 | 0.024 | 0.031 | 0.038 | 435 |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

* Strand count meets minimum number per ASTM

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Weights and Measurements (Metric)

| | | | | | | | | | | | | | |
|--------|-----|---|----|------|----|-------|------|--------|-------|------|------|--------|-----|
| 669288 | 750 | 1 | 53 | 3.18 | BK | 29.72 | 1409 | 147.32 | 20025 | 0.08 | 0.10 | 0.1247 | 435 |
|--------|-----|---|----|------|----|-------|------|--------|-------|------|------|--------|-----|





All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
* Strand count meets minimum number per ASTM
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Stock Code and Color (Other than Black)

| Stock Code | Size AWG | Color |
|------------|----------|-------|
| 672572 | 350 | Red |
| 663032 | 600 | Red |
| 669289 | 750 | Red |

