

## AL XLPE Type RPVU90 2KV

Single Aluminum Conductors, 1000V/2000V, 90°C MAX - 40°C MIN, Sunlight Resistant and FT4 Flame Test Rated




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** AlumaFlex® Compact Stranded Aluminum Alloy (AA-8176)
- Insulation:** Cross Linked Polyethylene (XLPE)

### APPLICATIONS AND FEATURES:

Single aluminum conductor with low temperature, moisture resisting XLPE (cross linked polyethylene) insulation. Sunlight Resistant. This product meets the current RoHS requirements. No lead is added or used in manufacturing.

### SPECIFICATIONS:

- ASTM B836 Compact Rounded Stranded Aluminum Conductors
- CSA C22.2 No. 38 Thermoset-insulated wires and cables
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)
- RoHS Compliant Lead-Free, Silicone-Free
- AA 8176 Stranded Aluminum Alloy Conductors
- CSA Standard C22.2 No. 271 Photovoltaic Cables

### SAMPLE PRINT LEGEND:

{SQMTR} SOUTHWIRE LL90458 {CSA} XXX KCMIL (XX{mm<sup>2</sup>}) COMPACT AL. --- {ALUMAFLEX}® AA8176 RPVU90 1000V/2000V XLPE FT1 (-40°C) SR DIR BUR RoHS

**Table 1 – Weights and Measurements**

| Cond. Size | Cond. Number | Strand | Insul. Thickness | Insulation Color | Approx. OD | Approx. Weight | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance @ 60Hz | Allowable Ampacity In Raceway 90°C† |
|------------|--------------|--------|------------------|------------------|------------|----------------|--------------------|------------------|----------------------|----------------------|----------------------------|-------------------------------------|
| AWG/Kcmil  |              | No.    | mil              |                  | inch       | lb/1000ft      | inch               | lb               | Ω/1000ft             | Ω/1000ft             | Ω/1000ft                   | Amp                                 |
| 2/0        | 1            | 19     | 95               | BK               | 0.566      | 198            | 2.2                | 798              | 0.133                | 0.160                | 0.043                      | 150                                 |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Strand count meets minimum number per ASTM

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Weights and Measurements (Metric)**

|     |   |    |      |    |       |     |       |      |      |      |        |     |
|-----|---|----|------|----|-------|-----|-------|------|------|------|--------|-----|
| 2/0 | 1 | 19 | 2.41 | BK | 14.38 | 295 | 55.88 | 3551 | 0.44 | 0.52 | 0.1411 | 150 |
|-----|---|----|------|----|-------|-----|-------|------|------|------|--------|-----|

All dimensions are nominal and subject to normal manufacturing tolerances





◊ Cable marked with this symbol is a standard stock item  
\* Strand count meets minimum number per ASTM  
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Stock Code and Color (Other than Black)**

| Stock Code | Size AWG | Color |
|------------|----------|-------|
| 672572     | 350      | Red   |
| 663032     | 600      | Red   |
| 669289     | 750      | Red   |

