



# Transformer Riser Wire, Protected Ground Wire (PGW), Cathodic Protection (CP) Cables, LLDPE

Black Polyethylene Covered. Solid or Stranded Soft Drawn Copper Conductor




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Conductors are solid or stranded compressed copper
- Covering:** Black Linear Low Density Polyethylene (LLDPE) also known as High Molecular Weight Polyethylene (HMWPE)

## APPLICATIONS AND FEATURES:

Used as covered grounding conductors, protected ground wires (PGW), cathodic protection (CP) cables, or on transformers as connection between line conductor and transformer primary bushing in applications where protection from momentary contact from wildlife is needed. Although not treated as an insulation, the thermoplastic polyethylene covering does provide an increased level of protection from momentary grounded contacts caused by wildlife, excessive wind and tree limbs or other grounded objects in the proximity of the high voltage lead. May be used on distribution system voltages up to 35kV line-to-line.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- ICEA S-70-547 Weather Resistant Polyethylene Covers Conductors

**Table 1 – Weights and Measurements**

| Stock Number | Cond. Size | Cond. Strands | Diameter Over Conductor | Inner Layer Thickness | Approx. OD | Approx. Weight |
|--------------|------------|---------------|-------------------------|-----------------------|------------|----------------|
|              | AWG/Kcmil  | #             | inch                    | mil                   | inch       | lb/1000ft      |
| 109314       | 2          | 7             | 0.283                   | 45                    | 0.373      | 226            |

All dimensions are nominal and subject to normal manufacturing tolerances

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

