


# 3-Layer 15kV AAC CAMV™ Covered Conductor (Tree Wire or Spacer Cable)

An Alternative and Robust Design to Bare AAC Conductors to Harden the Electrical Grid. 3-Layer, 15kV, Covered Conductor, Concentrically Stranded AAC, Track-Resistant Crosslinked Polyethylene.



### **CONSTRUCTION:**

- 1. **Conductor:** Concentrically stranded AAC
- 2. **Strand Shield:** Semi-conducting cross linked polymer
- 3. Inner Layer: Low-Density Crosslinked Polyethylene (LDXLPE)
- 4. **Outer Layer:** High-Density Track-Resistant Crosslinked Polyethylene (HDTRXLPE)

## **APPLICATIONS AND FEATURES:**

- Used for primary and secondary overhead distribution where limited space is available or desired for rights-of-way. Installed the same as bare conductors, however, covering is effective in preventing direct shorts and instantaneous flashovers should tree limbs or other objects contact conductors in such close proximity.
- Tree Wire Used for spans where trees crowd the right-of-way, such as in wooded residential areas, when a minimum of interference with the environment is desired. Covering minimizes power outages due to conductor contact with tree limbs, reducing the need for frequent or severe trimming.
- Covered Aerial MV Cable (CAMV)/Spacer Cable Installed with other Covered Aerial MV cables and a supporting messenger
  through a series of space-maintaining devices (spacers). The resulting close-proximity configuration minimizes the amount of
  space and hardware required for line installation, particularly useful in congested areas.
- Covering Rated 90°C Normal and 130°C Emergency Operation. Unless adequate knowledge of the thermal characteristics of
  the environment is known, the permissible conductor temperature should be reduced by 10°C or in accordance with available
  data.

#### SPECIFICATIONS:

- ASTM B230 Aluminum, 1350-H19 Wire for Electrical Purposes
- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ICEA S-121-733 Tree Wire and Messenger Supported Spacer Cable





# **Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Strands	Diameter Over Conductor	Conductor Shield Thickness	Inner Layer Thickness	Outer Layer Thickness	Approx. OD	Approx. Weight	Rated Strength
	AWG/ Kcmil	#	inch	mil	mil	mil	inch	lb/1000ft	lb
662400	397.5	19	0.659	25	75	75	1.073	578	6399

All dimensions are nominal and subject to normal manufacturing tolerances

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

