



## Flat Parallel Pump Cable Type THW

600 Volts, Stranded Copper Conductors. Polyvinyl Chloride (PVC) Insulation. Water Well Cable, Moisture Resistant, Flat Parallel. Rated 75°C,



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Solid soft drawn or fully annealed bare copper per ASTM B3. Stranded class B compressed bare copper ASTM B8
- Insulation:** Polyvinyl Chloride (PVC) Type THW

### APPLICATIONS AND FEATURES:

For use in residential, farm and industrial water well applications. Grounded and ungrounded water well cable systems. Conductors are twisted and colored black, red, and yellow when supplied with three conductors and green ground. Cable is supplied without an overall jacket.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wires and Cables

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SUBMERSIBLE PUMP CABLE TYPE THW X AWG (X.XX{mm<sup>2</sup>}) W/GRD 600 VOLTS





**Table 1 – Weights and Measurements**

Stock Number	Cond. Size AWG/Kcmil	Cond. Number No.	Cond. Strands No.	Diameter Over Conductor inch	Insul. Thickness mil	Ground No. x AWG	Approx. OD inch	Approx. Weight lb/1000ft
563658◇	14	3	7	0.070	30	1 x 14	0.166 X 0.558	68

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◇ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

Cond. Size AWG/ Kcmil	DC Resistance @ 25°C Ω/1000ft	AC Resistance @ 90°C Ω/1000ft	Inductive Reactance Ω/1000ft	Max Pull Tension lb	Min Bending Radius inch	Allowable Ampacity At 75°C Amp	Allowable Ampacity At 90°C Amp
14	2.631	3.170	0.058	98	2.2	20	25

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing.

