



# Romex® Control & Signal Cable

Class 2 Cable for Low-Voltage Power-Limited Lighting Control and Dimming. 150 Volts. Copper Conductors. SIMpull® Jacket Designed for Easier Pulling.




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

- Conductor:** Solid copper per ASTM B3
- Insulation:** All phases are insulated with Polyvinyl Chloride (PVC)
- Jacket:** Polyvinyl Chloride (PVC) jacket utilizing SIMpull® Technology. Colored light: Blue

## APPLICATIONS AND FEATURES:

ROMEX® SIMpull® Low-Voltage Control & Signal Cable is a class 2 power-limited circuit cable for use in lighting control and dimming applications. Rated for 150 volts per NEC Article 725. Temperature range is -20°C to +60°C. Sunlight Resistant

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- UL 13 Power-Limited Circuit Cables
- UL 2556 Standard for Safety Wire and Cable Test Methods

## SAMPLE PRINT LEGEND:

SOUTHWIRE{R} 16 AWG CU 2/C E57497 (UL) TYPE CL2

**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Conductor Number	Diameter Over Conductor	Conductor Stranding	Insulation Thickness	Approx. OD	Copper Weight	Overall Weight
	AWG/ Kcmil		inch		mils	inch	lbs/1000ft	lbs/1000ft
16 AWG   Solid								
643505	16	2	0.050	Solid	6	0.106 X 0.186	16	22

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item





**Table 2 – Electrical and Engineering Data**

Cond. Size	Conductor Number	Min. Bend Radius	DC Resistance at 25°C	AC Resistance at 75°C	Inductive Reactance @ 60Hz	Allowable Ampacity Raceway 75°C	Allowable Ampacity Raceway 90°C
AWG/ Kcmil		Inches	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
16 AWG   Solid							
16	2	0.7	4.181	5.037	0.033	-	18

\* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

