

# Multi Conductor CL3R/ FPLR/ CMR/ CMG Non-Shielded

300V, 75°C, Multi-Conductor, Non-Shielded, Stranded Copper, CL3R/FPLR/CMR/CMG



Image not to scale. See Table 1 for dimensions.

#### **CONSTRUCTION:**

1. **Conductor:** Stranded bare copper per ASTM B8

2. Insulation: Polyvinyl Chloride (PVC)

3. Rip Cord: Rip cord for ease of jacket removal

4. **Jacket:** Gray Polyvinyl Chloride (PVC)

#### **APPLICATIONS AND FEATURES:**

For use in Remote Control, Signaling, and Power-Limited circuits per NEC Article 725. Sizes 22 AWG - 16 AWG can also be used as communication circuits per NEC Article 800. Can be used in security, sound and audio, speaker cable, public address, intercom, sound reinforcement, alarm and access control circuits and power-limited controls. The conductors are cabled together; lay length varies depending on conductor count and gauge size.

Flame Test: UL 1666

Cable Type: CL3R, also, CMR where UL permits (Sizes 16 AWG and smaller)

Voltage: 300 VoltsTemperature: 75°C

#### **SPECIFICATIONS:**

- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (22 AWG 16 AWG)

### **SAMPLE PRINT LEGEND:**

XX AWG XX/C E57497 c{UL}US CMR/CL3R/FPLR -- CMG FT4 MADE IN USA ROHS-2 COMPLIANT -- {MM/DD/YY} {HH:MM} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET





## Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Jacket Color
	AWG	No.	strands	inch	mil	inch	lb /1000ft	lb /1000ft	Ω /1000ft	Ω /1000ft	
18 AWG											
R40018-1	18	2	7	0.045	20	0.144	10	14	6.669	8.035	Gray

All dimensions are nominal and subject to normal manufacturing tolerances



<sup>♦</sup> Cable marked with this symbol is a standard stock item