



# Soundsational® Speaker Cable, General Purpose, Direct Burial

300V, 75°C, General Purpose Southwire Signal Speaker Cable, In-Wall Rated, Stranded Bare Copper CL3




Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Stranded Class K bare copper
2. **Insulation:** Polyvinyl Chloride PVC
3. **Jacket:** Polyvinyl Chloride PVC

## APPLICATIONS AND FEATURES:

Southwire Soundsational® direct burial speaker cable is suitable for installation as follows:

- In burial applications with or without conduit.
- In outdoor locations, exposed to sunlight and moisture.

## SPECIFICATIONS:

- UL 1424 Cables for Power-Limited Fire-Alarm Circuits
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (22 AWG - 16 AWG)
- CSA C22.2 No. 2556 / UL 2556 Cable Test Methods
- RoHS Compliant Lead-Free, Silicone-Free
- Sunlight Resistance

## SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE{R} SIGNAL{R} XXXX XX AWG X/C C(ETL)US MASTER-DESIGN TYPE CM/CL3/FPL/PLTC DIRECT BURIAL AUDIO CABLE SUN RES





**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Rectance
	AWG	No.	strands	inch	mil	inch	lb /1000ft	lb /1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft
14 AWG											
94542	14	2	105	0.073	20	0.238	26	38	2.814	3.391	0.058

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item

