



## **3/C CU 2000V EPDM/CPE Type G-GC Industrial Grade Cable 90°C. MSHA Approved**

Flexible Copper conductors, Ethylene Propylene Diene Monomer (EPDM) insulation, Single Layer Chlorinated Polyethylene (CPE) Jacket



Image not to scale. See Table 1 for dimensions.

### **CONSTRUCTION:**

1. **Conductor:** Bare, soft drawn, annealed, flexible, rope-lay stranded copper per ASTM B3/B172
2. **Separator Tape:** Non-conducting tape applied between the conductor and insulation to facilitate stripping
3. **Insulation:** Ethylene Propylene Diene Monomer (EPDM). Color coded black, white, red
4. **Ground Check:** One insulated, bare, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B3/B172
5. **Ground Conductors:** Two insulated, bare, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B3/B172
6. **Fillers:** Paper fillers applied as needed to round the cable core
7. **Reinforcement Binder:** Reinforcing binder with twine applied over the core
8. **Jacket:** Black, flame resistant, thermosetting Chlorinated Polyethylene (CPE)

### **APPLICATIONS AND FEATURES:**

Southwire Type G-GC cable is a heavy-duty industrial cable for use in flexible, portable, and extra-hard usage applications where equipment grounding is required per NEC Article 400. Suitable for continuous submersion in water – ideal for submersible pumps, marine application. Also suitable for use in light to medium-duty mining applications. Sunlight and oil resistant. Highly flexible and easy to work with in cold conditions. Not for use as permanent building wiring. Meets FT-5 Flame Test. cUL Listed.

### **SPECIFICATIONS:**

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 1650 Standard for Portable Power Cable
- CSA C22.2 No. 96 Portable Power Cables
- RoHS-2 (European Directive 2011/65/EU)

### **SAMPLE PRINT LEGEND:**

SOUTHWIRE(R) ROYAL(R) XXX AWG (XX.XXmm<sup>2</sup>) 3/C TYPE G-GC PORTABLE POWER CABLE E172226 (UL) 2000V 90C DRY 90C WET OIL RESISTANT 60(D)C SUN RES -- 156205 CSA TYPE G-GC 2000V -40C FT1 FT5 P-07-KA110009-MSHA (MADE IN USA)





**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Conductor	Insul. Thickness	Ground	Ground Check Size	Jacket Thickness	Approx. OD	Approx. Weight	Jacket Color
	AWG/Kcmil	No.	No.	inch	mil	No. x AWG	AWG	mil	inch	lb/1000ft	
570239	250	3	608	0.605	95	2 x 1	1x8	260	2.284	4691	BK

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

**Table 2 – Electrical and Engineering Data**

Cond. Size	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance	Min Bending Radius	Allowable Ampacity In Air 60°C	Allowable Ampacity In Air 75°C	Allowable Ampacity In Air 90°C
AWG/Kcmil	Ω/1000ft	Ω/1000ft	Ω/1000ft	inch	Amp	Amp	Amp
250	0.047	0.057	0.041	13.7	259	310	352

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

