



## 4/C CU 2000V EPDM/CPE Type G Industrial Grade Cable 90°C. MSHA Approved

Flexible Copper conductors, Ethylene Propylene Diene Monomer (EPDM) insulation, Single Layer Chlorinated Polyethylene (CPE) Jacket



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Bare, soft drawn, annealed, flexible, rope-lay stranded copper per ASTM B3/B172
2. **Separator Tape:** Non-conducting tape applied between the conductor and insulation to facilitate stripping
3. **Insulation:** Ethylene Propylene Diene Monomer (EPDM). Color coded black, white, blue, red for sizes #4/0 and smaller and black, white, red, orange for sizes over 250 kcmil
4. **Ground Conductors:** Four insulated, bare, soft drawn, annealed, rope stranded, flexible lay copper per ASTM B3/B172
5. **Fillers:** Jute fillers applied as needed to round the cable core
6. **Reinforcement Binder:** Reinforcing binder with twine applied over the core
7. **Jacket:** Black, flame resistant, thermosetting Chlorinated Polyethylene (CPE)

### APPLICATIONS AND FEATURES:

Southwire Type G cable is a heavy-duty industrial cable for use in flexible, portable, and extra-hard usage applications where equipment grounding is required per NEC Article 400. Suitable for continuous submersion in water – ideal for submersible pumps, marine application. Also suitable for use in light to medium-duty mining applications. Sunlight and oil resistant. Highly flexible and easy to work with in cold conditions. Not for use as permanent building wiring. Meets FT-5 Flame Test. cUL Listed.

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 1650 Standard for Portable Power Cable
- MSHA Approved
- RoHS-2 (European Directive 2011/65/EU)

### SAMPLE PRINT LEGEND:

2 AWG 4/C TYPE G PORTABLE POWER CABLE 90°C WET OR DRY 2000V OIL AND SUN RES (UL) P-136-35-MSHA AIWTM c(UL) FT1/FT5 (-40°C)





**Table 1 – Weights and Measurements**

| Stock Number | Cond. Size    | Cond. Number | Cond. Strands | Diameter Over Conductor | Insul. Thickness | Ground       | Jacket Thickness | Approx. OD | Approx. Weight | Jacket Color |
|--------------|---------------|--------------|---------------|-------------------------|------------------|--------------|------------------|------------|----------------|--------------|
|              | AWG/<br>Kcmil | No.          | No.           | inch                    | mil              | No. x<br>AWG | mil              | inch       | lb/1000ft      |              |
| 562086       | 4/0           | 4            | 532           | 0.530                   | 80               | 4 x 4        | 155              | 2.175      | 4392           | BK           |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

**Table 2 – Electrical and Engineering Data**

| Cond. Size    | DC Resistance @ 25°C | AC Resistance @ 90°C | Inductive Reactance | Min Bending Radius | Allowable Ampacity In Air 60°C | Allowable Ampacity In Air 75°C | Allowable Ampacity In Air 90°C |
|---------------|----------------------|----------------------|---------------------|--------------------|--------------------------------|--------------------------------|--------------------------------|
| AWG/<br>Kcmil | Ω/1000ft             | Ω/1000ft             | Ω/1000ft            | inch               | Amp                            | Amp                            | Amp                            |
| 4/0           | 0.055                | 0.067                | 0.041               | 13.0               | 186                            | 222                            | 253                            |

\* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

