



## Flexible Hook-Up Wire/Appliance Wire Style 1061/M16878 "Type B"

80°C Dry. 300 Volts. Flexible Stranded Copper Conductor. PVC Insulation.



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class K, stranded bare or tinned copper per ASTM B3 or B33 and B174
2. **Insulation:** Polyvinyl Chloride (PVC). All colors available; Stripes available upon request

### APPLICATIONS AND FEATURES:

Designed for internal wiring in electric bookkeeping, accounting, time-recording machines, or electronic equipment within a chassis or protected from mechanical injury.

- AWM Style 1061: 80°C Dry, 300V
- AWM I A/B: 105°C Dry, 600V
- M16878 Type B: 105°C Dry, 600V

Rated for VW-1 and FT1

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 758 Standard for Appliance Wiring Material
- CSA C22.2 No. 210 Appliance Wiring Material Products
- Military Spec - M16878 Type B/1

### SAMPLE PRINT LEGEND:

XX AWG (XX{mm<sup>2</sup>}) E57498 {RU} AWM 1061 80C 300V VW-1 --- 156205 {CSA} AWM I A/B 80C 300V FT1 SR PVC --- M16878/1BJ 600V 105C TYPE B SW





**Table 1 – Physical and Electrical Data**

| Stock Number | Cond. Size | Cond. Number | Cond. Strands | Cond. Metal | Diameter Over Cond. | Insul. Thickness | Approx. OD | Approx. Weight | DC Resistance @ 25°C | AC Resistance @ 75°C |
|--------------|------------|--------------|---------------|-------------|---------------------|------------------|------------|----------------|----------------------|----------------------|
|              | AWG        | No.          | strands       |             | inch                | mil              | inch       | lb /1000ft     | Ω /1000ft            | Ω /1000ft            |
| AWM          |            |              |               |             |                     |                  |            |                |                      |                      |
| F20059       | 20         | 1            | 10            | TCu         | 0.037               | 9                | 0.058      | 4              | 11.319               | 13.638               |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.



Ampacity

