



## 300V AMERICAN MUSTANG® SAFEGUARD™ Type SJOOW Cord with Yellow Jacket 105°C. MSHA Approved

300V, 105°C Flexible Cord. Heat, Moisture and Oil Resistant EPDM Rubber Insulation and Heat, Moisture and Oil Resistant Flexible CPE Jacket, UL/CSA Listed.



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant EPDM
3. **Filler:** Waxed paper
4. **Separator:** Paper separator wrapped around the assembly
5. **Jacket:** Yellow CPE (Other colors available upon request)

### APPLICATIONS AND FEATURES:

Southwire AMERICAN MUSTANG® SAFEGUARD™ Type SJOOW Flexible Cords are UL/ CSA listed and permitted for use as specified by Article 400 and related articles of the 2023 National Electrical Code®. The cable is rated -40°C to 105°C, water, oil, and weather resistant. SAFEGUARD™ Type SJOOW Flexible Cords are designed for hard usage on industrial equipment and tools in the food and beverage industry in Zone 2 Splash zone. Microbial additive helps to resist 99.9% of bacteria specifically S. Aureus and E. Coli.

### SPECIFICATIONS:

- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- Exceeds Ecolab PM-40-1 Material Resistance Test With 30-day Exposure, UL Verified V747862
- MSHA Approved
- RoHS-3 Complies with European Directive 2015/863

### SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® American Mustang® SAFEGUARD{TM} CORD X/C XX AWG (XX{mm2}) SJOOW E46194 {UL} 300V -40°C TO 105°C -- {CSA} LL90458 SJOOW 300V -40°C TO 105°C FT2 WATER RESISTANT --- P-07-KA190005-MSHA





**Table 1 – Weights and Measurements**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity	Jacket Color
	AWG/Kcmil	No.	No.	mil	mil	inch	lb/1000ft	Amp	
138667	18	3	16	30	35	0.303	54	7	Yellow

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Ampacities are based on TABLE 400.5(A) of the 2023 National Electrical Code and CEC Table 12.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Ampacity *	Jacket Color
	AWG/Kcmil	No.	No.	mm	mm	mm	kg/km	Amp	
138667	18	3	16	0.76	0.89	7.70	80	7	Yellow

\* Ampacities are based on TABLE 400.5(A) of the 2023 National Electrical Code and CEC Table 12.\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

**Color Code**

# of Conductor	Color Sequence
2	Black, White
3	Black, White, Green
4	Black, White, Red, Green

