



General Purpose Primary Automotive Wire (GPT)

80°C or 105°C. 60 Volts DC or 25 Volts AC. Flexible Stranded Copper Conductor. PVC Insulation.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Flexible stranded bare copper. Tinned copper available upon request
2. **Insulation:** Polyvinyl Chloride (PVC). All colors available; Stripes available upon request

APPLICATIONS AND FEATURES:

Intended for use at nominal system voltage of 60 Volts DC (25 Volts AC) or less in surface vehicle electrical systems.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- SAE J1128 Surface Vehicle Standard Low Voltage Primary Cable
- Ford ESF-M1L56 (80°C Wires)
- Chrysler MS-3450 (80°C Wires)
- Chrysler MS-3450 (105°C Wires)
- Ford ESF-M1L58-A (105°C Wires)



Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C
	AWG	No.	strands	inch	mil	inch	lb /1000ft	Ω /1000ft	Ω /1000ft
GPT									
F20013	20	0	7	0.037	23	0.084	6	11.319	13.638

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

