



Primary Automotive Lead Wire

125°C. 60 Volts DC or 25 Volts AC. Flexible Stranded Copper Conductor. XLPE Insulation.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Flexible stranded bare copper. Tinned copper available upon request
2. **Insulation:** Cross Linked Polyethylene (XLPE). All colors available; Stripes available upon request.

APPLICATIONS AND FEATURES:

Intended for use at nominal system voltage of 60 Volts DC (25 Volts AC) or less in surface vehicle electrical systems.

- GXL - General Purpose
- SXL - Special Purpose
- TXL - Thin Wall

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- SAE J1128 Surface Vehicle Standard Low Voltage Primary Cable
- Chrysler MS-8288
- Ford ESB-M1L85-A
- Chrysler MS-8900
- Chrysler MS-5919
- Ford ESB-M1L123A





Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C
	AWG	No.	strands	inch	mil	inch	lb /1000ft	Ω /1000ft	Ω /1000ft
GXL									
F20022	20	1	7	0.037	41	0.086	6	11.319	13.638

All dimensions are nominal and subject to normal manufacturing tolerances

∅ Cable marked with this symbol is a standard stock item

GXL meets Ford ESB-M1L85-A, Chrysler MS-8900

SXL meets Ford ESB-M1L85-A, Chrysler MS-5919

TXL meets Ford ESB-M1L123A, Chrysler MS-8288

