



Southwire® RenewaFLEX™ Power Cables for Battery Energy Storage Systems

Single Conductor Copper 2000V XLPE insulation Type RHH/RHW-2 Flexible Power Cable.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** 6 - 4/0 AWG: Class K, Flexible stranded bare copper. 250 - 750 kcmil: Class I, Flexible stranded bare copper
2. **Insulation:** Cross Linked Polyethylene (XLPE) Type RHH/RHW-2

APPLICATIONS AND FEATURES:

Southwire's 2000 Volt power cables are suited for use in the internal wiring of Battery Energy Storage Systems (BESS), in wet and dry locations, conduits, ducts, troughs, covered trays, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation, 130°C for emergency overload, and 250°C for short circuit conditions. Gasoline and Oil Resistant. For CT USE sizes 1/0 AWG and larger. Rated 1000 lbs./FT maximum sidewall pressure.

Also available in different colors like: Black, Red, Green, Brown, Yellow, etc.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test
- RoHS-3 Complies with European Directive 2015/863
- Made in America: Compliant with both Buy American and Buy America Act (BAA) requirements per 49 U.S.C. § 5323(j) and the Federal Transit Administration Buy America requirements per 49 C.F.R. part 661

SAMPLE PRINT LEGEND:

For 6-2 AWG: {SQFTG} SOUTHWIRE E30117 {UL} XX AWG CU TYPE RHH OR RHW-2 XX MILS XLP PRI/II GRI/II 2000 VOLTS

For 1/0-4/0 AWG: {SQFTG} SOUTHWIRE E30117 {UL} XX AWG CU TYPE RHH OR RHW-2 XX MILS XLP FOR CT USE PRI/II GRI/II 2000 VOLTS

For 250-750 kcmil: {SQFTG} SOUTHWIRE E30117 {UL} XX kcmil CU TYPE RHH OR RHW-2 XX MILS XLP FOR CT USE PRI/II GRI/II 2000 VOLTS





Table 1 – Weights and Measurements

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Insul. Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	inch	mil	inch	lb/1000ft
138951	750	1850	1.094	120	1.346	2650

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity In Raceway 90°C
AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp	Amp
750	10.6	6000	0.015	0.025	0.038	885	535

† Ampacities based upon 2023 NEC Table 310.16 for Raceway, Cable, or Earth.

† NEC Table 310.17 for single conductors in Air.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

Table 3 – Weights and Measurements (Metric)

Stock Number	Cond. Size	Strand	Diameter Over Conductor	Insul. Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	mm	mm	mm	kg/km
138951	750	1850	27.79	3.05	34.19	3944

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Air 90°C	Allowable Ampacity In Raceway 90°C
AWG/Kcmil	mm	newton	Ω/km	Ω/km	Ω/km	Amp	Amp
750	269.24	26700	0.0492	0.08	0.1247	885	535

† Ampacities based upon 2023 NEC Table 310.16 for Raceway, Cable, or Earth.

† NEC Table 310.17 for single conductors in Air.

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

