



SIS/XHHW-2 VW-1

90°C Wet/Dry. 600 Volts. Flexible Stranded Copper Conductor. XLPE Insulation.




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Flexible stranded tinned copper. Bare copper available upon request
2. **Insulation:** Cross Linked Polyethylene (XLPE). All colors available

APPLICATIONS AND FEATURES:

Designed for internal wiring of electrical equipment, control panels, appliances, and ground for use on industrial plan floor. For use as permitted by National Electrical Code® Article 310.

- SIS: 90°C Dry, 600V
- XHHW-2: 90°C Dry, 90°C Wet, 1000V
- RW90: 90°C Dry, 90°C Wet, 8 - 4/0 AWG 600V

Rated for Oil Res II, Gasoline Res II, VW-1, FT1, FT2 or FT4 (8 AWG and larger), and -40°C Cold Bend

SPECIFICATIONS:

- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B172 Standard Specification for Rope-Lay-Stranded Copper Conductors Having Bunch-Stranded Copper Conductors (As Applicable)
- ASTM B173 Rope-Lay-Stranded Copper Conductors Having Concentric-Stranded Members
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 44 Thermoset-Insulated Wires and Cables
- CSA C22.2 No. 38 Thermoset-insulated wires and cables

SAMPLE PRINT LEGEND:

14 - 10 AWG

XX AWG (XXmm²) CLASS K E30117 (UL) XHHW-2 SR PR II GR II OR SIS 90C 1000V VW-1 -- 156205 CSA SIS 90C 600V -40C FT1 FT2 VW-1

8 - 4/0 AWG

XX AWG (XXmm²) E30117 (UL) XHHW-2 SR PR II GR II OR SIS 90C 1000V VW-1 -- 156205 CSA RW90 90C DRY/90C WET 600V PRI -40C FT1 FT4 OR SIS 90C 600V -40C FT1 FT2 VW-1





Table 1 – Physical and Electrical Data

Stock Number	Cond. Size AWG	Cond. Number No.	Cond. Strands strands	Diameter Over Cond. inch	Insul. Thickness mil	Approx. OD inch	Approx. Weight lb /1000ft	DC Resistance @ 25°C Ω /1000ft
XHHW-2 / SIS / RW90								
18808	8	1	133	0.149	45	0.247	71	0.679

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

