



Bare Copper Solid, Compressed Class B and C



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Bare copper solid or compressed class B or C per ASTM B3 and ASTM B8

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors

Table 1 – Physical and Electrical Data

| Stock Number | Cond. Size | Strand Class | Strand Count | Cond. Cmil | Diameter Over Conductor | Approx. OD | Approx. Weight | DC Resistance @ 25°C | AC Resistance @ 75°C | Rated Strength |
|---------------------|---------------|--------------|----------------|------------|-------------------------|------------|----------------|----------------------|----------------------|----------------|
| | AWG/ kcmil | | No. of Strands | cmil | inch | inch | lb/1000ft | Ω/1000ft | Ω/1000ft | lb |
| 106443 [◇] | 4 | Solid | Solid | 41740 | 0.204 | 0.204 | 128 | 0.258 | 0.310 | 333 |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item

