



Broadband Coax - RG11 Dual and Quad Shield




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

Non-Plenum Rated

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Aluminum foil and braid shielded
4. **Jacket:** Polyvinyl Chloride PVC.

Plenum Rated

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Foamed Fluoropolymer
3. **Shield:** Aluminum foil and braid shielded
4. **Jacket:** Low smoke Polyvinyl Chloride PVC. Polyethylene for outdoors

APPLICATIONS AND FEATURES:

- CATV Applications for distributing television signals
- ALUMINUM BRAID CCTV Applications for surveillance
- Connecting security cameras, DVR or monitor using "BNC" connectors
- COPPER BRAID
- 75 Ohms Impedance

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SIGNAL® 992165 RG11 XX AWG CCS QUAD SHIELD 40/60% AL BRAID E57497 (UL) CM OR CL2 OR CATV 75°C SUN RES SWEPT TO 3.0 GHZ

{SQFTG} SOUTHWIRE® SIGNAL® 821013 RG11 XX AWG CCS DUAL SHIELD 60% AL BRAID E57497 (UL) TYPE CMP/CL2P/ CATVP 125°C -- C(UL) CMP FT6 SWEPT TO 3.0 GHZ

{SQFTG} SOUTHWIRE® SIGNAL® RG11/U DIRECT BURIAL



Table 1 – Physical and Electrical Data

| Stock Number | Cable Type | Rating | Cond. Size | Cond. Number | Cond. Type | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Shield Type | Application |
|--------------|------------|--------------------|------------|--------------|------------|---------------|------------------|------------------|------------|----------------|-------------|-----------------|
| | | | AWG | No. | | strands | mil | mil | inch | lb /1000ft | | |
| RG11 | | | | | | | | | | | | |
| 992153 | RG11 | CM/CL2/ UL-1581 | 14 | 1 | BC | Solid | 110 | 40 | 0.404 | 57 | Dual | CATV/Sun Res |

All dimensions are nominal and subject to normal manufacturing tolerances
 ◇ Cable marked with this symbol is a standard stock item