

## **Broadband Coax - RG8, RG62, RG174, RG213, RG214, RG223**

**Southwire®****Quad Shield****Southwire®****Dual Shield**

4

3

2

1

Image not to scale. See Table 1 for dimensions.

**CONSTRUCTION:**

- Conductor:** Bare copper or copper clad steel
- Insulation:** Polyethylene
- Shield:** Copper braid shielded
- Jacket:** Polyvinyl Chloride PVC.

**APPLICATIONS AND FEATURES:**

CATV Applications for distributing television signals, using "F" connectors, ALUMINUM BRAID CCTV Applications for surveillance; Connecting security cameras, DVR or monitor using "BNC" connectors, COPPER BRAID

**Table 1 – Physical and Electrical Data**

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Shield Type
			AWG	No.		strands	mil	mil	inch	lb /1000ft	
RG174											
991069	RG174	AWM Style 1354, UL 1	26	1	CCS	7	20	10	0.100	8	Tinned Cu Braid

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item