



## Broadband Coax - RG8, RG62, RG174, RG213, RG214, RG223




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Copper braid shielded
4. **Jacket:** Polyvinyl Chloride PVC.

### APPLICATIONS AND FEATURES:

CATV Applications for distributing television signals, using "F" connectors, ALUMINUM BRAID CCTV Applications for surveillance; Connecting security cameras, DVR or monitor using "BNC" connectors, COPPER BRAID



Table 1 – Physical and Electrical Data

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Shield Type	Application
			AWG	No.		strands	mil	mil	inch	lb /1000ft		
RG8												
991020	RG8	CL2, AWM Style 1354,	17	1	BC	Solid	45	30	0.240	37	Dual	CATV

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item