Bare Copper Solid or Compressed




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid bare copper per ASTM B3 or Class A, B, or C, compressed, stranded, bare copper per ASTM B3 and B8

APPLICATIONS AND FEATURES:

Bare copper conductors are suitable for overhead transmission and distribution as well as grounding and general electrical constructions. Stranded conductors (Class A) are ideal for Overhead transmission and distribution lines. More flexible stranded designs (Class B and C) work well for uninsulated connections, jumpers, grounding, or insulated cables for general wiring and underground systems.

Features:

- The conductor is manufactured from Electrolytic Tough Pitch (ETP) copper, designated as Unified Numbering System (UNS) C11000, which applies to all copper products regardless of temper or stranding classification.
- Soft-drawn copper exhibits an electrical conductivity of 100% at 20°C in accordance with the International Annealed Copper Standard (IACS).
- Copper purity is at least 99.9%, with total impurities, including oxygen and other trace elements, limited to a maximum of 0.1%.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors

Table 1 – Physical and Electrical Data

Cond. Size	Strand Class	Strand Count	Cond. Cmil	Cond. Number	Diameter Over Conductor	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C
AWG/ kcmil		No. of Strands	cmil	No.	inch	inch	lb/1000ft	Ω/1000ft	Ω/1000ft
1	SOLID	SOLID	83690	1	0.289	0.289	258	0.128	0.159

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

We've got it MADE IN AMERICA

Copyright © 2026 Southwire Company, LLC. All Rights Reserved