



Bare Copper Solid, Compressed Class B and C



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Bare copper solid or compressed class B or C per ASTM B3 and ASTM B8

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors

Table 1 – Physical and Electrical Data

| Stock Number | Cond. Size | Strand Class | Strand Count | Cond. Cmil | Diameter Over Conductor | Approx. OD | Approx. Weight | DC Resistance @ 25°C | AC Resistance @ 75°C | Rated Strength |
|---------------------|---------------|--------------|----------------|------------|-------------------------|------------|----------------|----------------------|----------------------|----------------|
| | AWG/ kcmil | | No. of Strands | cmil | inch | inch | lb/1000ft | Ω/1000ft | Ω/1000ft | lb |
| 207852 [◇] | 350 | C | 61 | 350000 | 0.681 | 0.681 | 1081 | 0.031 | 0.039 | 2800 |

All dimensions are nominal and subject to normal manufacturing tolerances

◇ Cable marked with this symbol is a standard stock item