



Broadband Coax - RG59 Dual Shield




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Aluminum braid shielded
4. **Jacket:** Polyvinyl Chloride PVC.

APPLICATIONS AND FEATURES:

- CATV Applications for distributing television signals
- ALUMINUM BRAID CCTV Applications for surveillance
- Connecting security cameras, DVR or monitor using "BNC" connectors
- COPPER BRAID
- 75 Ohms Impedance

SPECIFICATIONS:

- UL 1685 Vertical-Tray Fire Propagation and Smoke Release Test

SAMPLE PRINT LEGEND:

{SQFTG} SOUTHWIRE® SIGNAL® 92006 RG59 XX AWG CCS DUAL SHIELD E57497 (UL) CM OR CL2 OR CATV 75°C SUN RES



Table 1 – Physical and Electrical Data

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Shield Type	Application
			AWG	No.		strands	mil	mil	inch	lb /1000ft		
RG59												
92009	RG59	CM/CL2	22	1	CCS	Solid	60	30	0.240	20	Dual	CATV

All dimensions are nominal and subject to normal manufacturing tolerances
 ◊ Cable marked with this symbol is a standard stock item