Broadband Coax - RG8, RG62, RG174, RG213, RG214, RG223



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Bare copper or copper clad steel

Insulation: Polyethylene
Shield: Copper braid shielded
Jacket: Polyvinyl Chloride PVC.

APPLICATIONS AND FEATURES:

CATV Applications for distributing television signals, using "F" connectors, ALUMINUM BRAID CCTV Applications for surveillance; Connecting security cameras, DVR or monitor using "BNC" connectors, COPPER BRAID



Table 1 – Physical and Electrical Data

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Shield Type
			AWG	No.		strands	mil	mil	inch	lb /1000ft	
RG214											
991075	RG214	CL2X, AWM Style 1354	12.7	1	scc	Solid	95	40	0.425	138	Quad

All dimensions are nominal and subject to normal manufacturing tolerances

[♦] Cable marked with this symbol is a standard stock item