



## Broadband Coax - RG8, RG62, RG174, RG213, RG214, RG223




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Bare copper or copper clad steel
2. **Insulation:** Polyethylene
3. **Shield:** Copper braid shielded
4. **Jacket:** Polyvinyl Chloride PVC.

### APPLICATIONS AND FEATURES:

CATV Applications for distributing television signals, using "F" connectors, ALUMINUM BRAID CCTV Applications for surveillance; Connecting security cameras, DVR or monitor using "BNC" connectors, COPPER BRAID



**Table 1 – Physical and Electrical Data**

Stock Number	Cable Type	Rating	Cond. Size	Cond. Number	Cond. Type	Cond. Strands	Insul. Thickness	Jacket Thickness	Approx. OD	Approx. Weight	Shield Type	Application
			AWG	No.		strands	mil	mil	inch	lb /1000ft		
RG174												
991069	RG174	AWM Style 1354, UL 1	26	1	CCS	7	20	10	0.100	8	Tinned Cu Braid	CATV

All dimensions are nominal and subject to normal manufacturing tolerances  
 ◇ Cable marked with this symbol is a standard stock item