

# **CU 600V PVC Insulation PVC Jacket Mini Split Type TC-ER-JP**

CU 600V PVC Insulation PVC Jacket Mini Split Type THHN/THWN Rated at 75°C Wet 90°C Dry




Image not to scale. See Table 1 for dimensions.

## **CONSTRUCTION:**

- Conductor:** Solid or stranded bare copper per ASTM B3 or B8
- Insulation:** Polyvinyl Chloride PVC with Nylon sheath
- Filler:** Polypropylene filler
- Binder:** Polyester flat thread binder tape
- Overall Jacket:** Polyvinyl Chloride (PVC) Jacket

## **APPLICATIONS AND FEATURES:**

Southwire's 600 Volt Type TC-ER-JP control cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 75°C in wet locations and 90°C in dry locations, 105°C for emergency overload, and 150°C for short circuit conditions. For uses in Class I, II, and III, Division 2 hazardous locations per NEC Article 501 and 502. Constructions with 3 or more conductors are listed for exposed runs (TC-ER) per NEC 336.10. Sunlight Resistant - For Direct Burial - Silicone Free - VW-1 Rated.

## **SPECIFICATIONS:**

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 83 Thermoplastic Insulated Wire and Cables (sizes 14 AWG to 1000 kcmil)
- UL 1277 Electrical Power and Control Tray Cables
- RoHS-3 Complies with European Directive 2015/863

## **SAMPLE PRINT LEGEND:**

{SQFTG} SOUTHWIRE{R} E75755 {UL} XX AWG (X.XX{mm2}) CU 7 CDRS TYPE TC-ER-JP THHN OR THWN CDRS 90{D}C  
JACKET SUNLIGHT RESISTANT DIRECT BURIAL 600 VOLTS {NOM}-ANCE



**Table 1 – Physical and Electrical Data**

| Stock Number  | Cond. Size | Cond. Number | Cond. Strands | Diameter Over Cond. | Insulation Color              | Insul. Thickness | Ground    | Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight | DC Resistance @ 25°C | AC Resistance @ 75°C | Inductive Reactance | Min Bending Radius | Allowable Ampacity 75°C |
|---------------|------------|--------------|---------------|---------------------|-------------------------------|------------------|-----------|------------------|------------|---------------|----------------|----------------------|----------------------|---------------------|--------------------|-------------------------|
|               | AWG        | No.          | strands       | inch                |                               | mil              | No. x AWG | mil              | inch       | lb / 1000ft   | lb / 1000ft    | Ω /1000ft            | Ω /1000ft            | Ω/1000ft            | inch               | Amp                     |
| <b>14 AWG</b> |            |              |               |                     |                               |                  |           |                  |            |               |                |                      |                      |                     |                    |                         |
| 408633◊       | 14         | 7            | 7             | 0.070               | BK, RD, BE, OE, YW, BN, RD/BK | 20               | 1 x 14    | 45               | 0.429      | 90            | 151            | 2.631                | 3.170                | 0.058               | 1.7                | 14                      |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

