




# Romex® Brand Copper SIMpull® Indoor NM-B Cable 3 Conductors

Nonmetallic-Sheathed Cable. 600 Volt. Copper Conductor. PVC Insulation/Nylon Sheath. White PVC Jacket with SIMpull® Technology for Easier Pulling.



#12 AWG  #14 AWG   
#10 AWG

Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Solid copper per ASTM B3
2. **Insulation:** All phases and neutral(s) are insulated with Polyvinyl Chloride (PVC) with Nylon Sheath
3. **Ground:** Solid soft drawn bare copper with kraft paper wrap
4. **Binder:** Kraft paper
5. **Jacket:** Polyvinyl Chloride (PVC) jacket utilizing SIMpull® Technology

## APPLICATIONS AND FEATURES:

Southwire® Romex® Brand SIMpull® NM-B (nonmetallic-sheathed) cable may be used for both exposed and concealed work in dry locations as specified in the National Electrical Code®. NM-B cable is primarily used in residential wiring as branch circuits for outlets, switches, and other loads. NM-B cable may be run in air voids of masonry block or tile walls where such walls are not wet or damp locations. Voltage rating for NM-B cable is 600 volts.

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- UL 719 Nonmetallic-Sheathed Cables
- Federal Specification A-A-59544
- NOM-063-SCFI Electrical Products – Conductors – Safety Requirements

## SAMPLE PRINT LEGEND:

E18679 (UL) ROMEX(R) SIMpull(TM) XX AWG (X.XXmm<sup>2</sup>) CU 3 CDR WITH XX AWG (X.XXmm<sup>2</sup>) GROUND TYPE NM-B 600 VOLTS NOM-ANCE

**Table 1 – Weights and Measurements**

Cond. Size	Cond. Number	Strand Count	Diameter Over Conductor	Insul. Thickness	Ground	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
AWG/ Kcmil		No. of Strands	inch	mil	No. x AWG	mil	inch	lb/1000ft	lb/1000ft
14	3	Solid	0.064	20	1 x 14	30	0.478 X 0.176	49	81

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item





**Table 2 – Electrical and Engineering Data**

Cond. Size AWG/Kcmil	Cond. Number	Min Bending Radius inch	Max Pull Tension lb	DC Resistance @ 25°C Ω/1000ft	AC Resistance @ 75°C Ω/1000ft	Inductive Reactance @ 60Hz Ω/1000ft
14	3	0.7	98	2.631	3.170	0.058

\* Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.

