



## Multi Conductor CL3P/FPLP/CMP Shielded

300V, 75°C, Multi-Conductor, Shielded, Stranded Copper, CL3P/FPLP/CMP



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Stranded bare copper per ASTM B8
2. **Insulation:** Low Smoke Polyvinyl Chloride (LS-PVC)
3. **Shield:** Aluminum foil shield with 24 AWG tinned drain wire
4. **Rip Cord:** Rip cord for ease of jacket removal
5. **Jacket:** White Low Smoke Polyvinyl Chloride (LS-PVC)

### APPLICATIONS AND FEATURES:

For use in Remote Control, Signaling, and Power-Limited circuits per NEC Article 725. Sizes 22 AWG - 16 AWG can also be used as communication circuits per NEC Article 800. Can be used in security, sound and audio, speaker cable, public address, intercom, sound reinforcement, alarm and access control circuits and power-limited controls. The conductors are cabled together; lay length varies depending on conductor count and gauge size.

### SPECIFICATIONS:

- UL 1424 Cables for Power-Limited Fire-Alarm Circuits
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 13 Power-Limited Circuit Cables
- UL 444 Communications Cables (22 AWG - 16 AWG)
- NFPA 262

### SAMPLE PRINT LEGEND:

XXAWG XX/C E57497 c{UL}US CMP/CL3P/FPLP 75°C -- CMP FT6 MADE IN USA ROHS-2 COMPLIANT -- {MM/DD/YY}  
{HH:MM} {SEQUENTIAL FOOTAGE MARKS} SEQ FEET





**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insulation Color	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Min Bending Radius	Jacket Color
	AWG	No.	strands	inch		mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	inch	
18 AWG														
P40073-1◇	18	4	7	0.045	BK, RD, WE, GN	9	15	0.186	21	33	6.669	8.035	0.7	White

All dimensions are nominal and subject to normal manufacturing tolerances  
◇ Cable marked with this symbol is a standard stock item

