



Covered Line Wire With Crosslinked Polyethylene (XLPE)

Aluminum Conductor Covered with Black Crosslinked Polyethylene



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Conductors are solid or stranded compressed aluminum
2. **Insulation:** Black Crosslinked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Aluminum alloy 1350-H19 or 6201 concentrically stranded. Covered with crosslinked polyethylene (XLP). Used primarily for, but not limited to, overhead secondary distribution lines. Installed on insulators, otherwise treated as a bare conductor. Crosslinked covered line wires have the below temperature ratings:

- Normal Service temperature of 90°C
- Emergency Overload of 130°C
- Short Circuit temperature of 250°C

SPECIFICATIONS:

- ASTM B230 Aluminum, 1350-H19 Wire for Electrical Purposes
- ASTM B231 Standard Specification for Concentric-Lay-Stranded Aluminum 1350 Conductors
- ASTM B400 Standard Specification for Compact Round Concentric-Lay-Stranded, Aluminum 1350 Conductors
- ICEA S-70-547 Weather Resistant Polyethylene Covers Conductors



Table 1 – Weights and Measurements

Stock Number	Code Word	Phase Cond. Size AWG/Kcmil	Phase Strand No.	Phase Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
148130	Chinquapin	350	19	60	0.778	390

All dimensions are nominal and subject to normal manufacturing tolerances

Table 2 – Electrical and Engineering Data

Code Word	Phase Cond. Size AWG/Kcmil	Neutral Rated Breaking Strength lb	Allowable Ampacity In Air 90°C Amp
Chinquapin	350	5751	506

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.