



Covered Line Wire With Crosslinked Polyethylene (XLPE) - ACSR

ACSR Covered with Black Crosslinked Polyethylene




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Stranded compressed aluminum steel reinforced ACSR
2. **Insulation:** Black Crosslinked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Aluminum alloy 1350-H19 concentrically stranded steel reinforced ACSR. Covered with crosslinked polyethylene (XLP). Used primarily for, but not limited to, overhead secondary distribution lines. Installed on insulators, otherwise treated as a bare conductor. Crosslinked covered line wires have the below temperature ratings:

- Normal Service temperature of 90°C
- Emergency Overload of 130°C
- Short Circuit temperature of 250°C

SPECIFICATIONS:

- ASTM B232 Concentric-Lay-Stranded, Aluminum Conductors, Coated Steel Reinforced (ACSR)
- ICEA S-70-547 Weather Resistant Polyethylene Covers Conductors





Table 1 – Weights and Measurements

Code Word	Phase Cond. Size AWG/Kcmil	Phase Strand No.	Phase Insul. Thickness mil	Approx. OD inch	Approx. Weight lb/1000ft
Butternut	4	6/1	30	0.310	72

All dimensions are nominal and subject to normal manufacturing tolerances

Table 2 – Electrical and Engineering Data

Code Word	Phase Cond. Size AWG/Kcmil	Neutral Rated Breaking Strength lb	Allowable Ampacity In Air 90°C Amp
Butternut	4	1770	495

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

