



Covered Line Wire With Crosslinked Polyethylene (XLPE) - ACSR

ACSR Covered with Black Crosslinked Polyethylene




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Stranded compressed aluminum steel reinforced ACSR
2. **Insulation:** Black Crosslinked Polyethylene (XLPE)

APPLICATIONS AND FEATURES:

Aluminum alloy 1350-H19 concentrically stranded steel reinforced ACSR. Covered with crosslinked polyethylene (XLP). Used primarily for, but not limited to, overhead secondary distribution lines. Installed on insulators, otherwise treated as a bare conductor. Crosslinked covered line wires have the below temperature ratings:

- Normal Service temperature of 90°C
- Emergency Overload of 130°C
- Short Circuit temperature of 250°C

SPECIFICATIONS:

- ASTM B232 Concentric-Lay-Stranded, Aluminum Conductors, Coated Steel Reinforced (ACSR)
- ICEA S-70-547 Weather Resistant Polyethylene Covers Conductors





Table 1 – Weights and Measurements

Code Word	Phase Cond. Size	Phase Strand	Phase Insul. Thickness	Approx. OD	Approx. Weight
	AWG/Kcmil	No.	mil	inch	lb/1000ft
Hickory	4	7/1	30	0.317	83

All dimensions are nominal and subject to normal manufacturing tolerances

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Code Word	Phase Cond. Size	Neutral Rated Breaking Strength	Allowable Ampacity In Air 75/90°C
	AWG/Kcmil	lb	Amp
Hickory	4	2240	105

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

