



## Bronze and Alloy, Grooved Contact Wire

CuMg 0.2 (Alloy80)/CuMg 0.5 (Alloy 55) Contact CuAg0.1 and CuSn0.2/ Trolley Wire



Image not to scale. See Table 1 for dimensions.

Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

This product combines excellent wear characteristics, and high-tensile strength properties. Contact/ Trolley wire is available in a choice of two alloys to provide the best match of electrical and mechanical wear properties for each application - 55 percent and 80 percent conductivity IACS (CA165 and A162), and is offered in both ASTM and EN/IEC configurations: round (upon request), grooved, figure 8, or figure 9.

### APPLICATIONS AND FEATURES:

For use as overhead power source on streetcars, trolleys, electric trolley buses, light rail and heavy mass transit systems. Also used on electrically powered mine train, and industrial cranes. High-tensile strength properties allow for reduced clearance maintenance in tunnel applications. Southwire bronze contact/trolley wire is ideal for transportation systems with increased line speeds just over 200 mph (322 km/h).

- High Tensile Strength and Breaking Load
- Highest Half-Hard Value of any Materials in Present Day Use.
- Durable and Reliable Support.
- Allows for Increase in Max Line Speeds
- Mechanically Rugged
- RoHS/Proposition 65 Compliant
- Ships on N-42 wooden reels (S-77 steel reels available per SW reel policy)
- Available with top lobe identification marking per IEEE 1896-2016
- Southwire SPEED Qualified for low volume requests
- Buy America Compliant

### SPECIFICATIONS:

- ASTM B9 Bronze Trolley Wire
- EN 50149 Railway Applications. Fixed Installations. Electric Traction. Copper and Copper Alloy Grooved Contact Wires.

**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size AWG/kcmil	Cond. Cmil cmil	Alloy	Cond. Shape	Approx. OD inch	Approx. Weight lb/1000ft	DC Resistance @ 25°C Ω/1000ft	Rated Strength lb
646818	350	351200	CuMg0.2	grooved	0.62	1063	0.037	16410

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item





**Contact Wire**

