CU 150V HVAC Wire Unshielded Thermostat CL2/CMH

CU 150V HDPE Insulation PVC Jacket CL2/CMH Power Limited Unshielded Thermostat Wire




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Solid bare copper per ASTM B3
2. **Insulation:** High Density Polyethylene HDPE
3. **Rip Cord:** Rip cord for ease of jacket strip ability
4. **Overall Jacket:** Polyvinyl Chloride (PVC) Jacket in Brown

APPLICATIONS AND FEATURES:

- 150 Voltage
- rating per NEC® Article 725
- ETL listed to UL 13 and UL 444
- Meets UL 1581 Vertical Tray Flame Test (FT-1)
- Type CL2
- C22.2 214 TYPE CMH

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- UL 13 Power-Limited Circuit Cables
- UL 444 CM/CL2

SAMPLE PRINT LEGEND:

TYPE CL2 C{ETL}US XX AWG XX/C BAROSTAT II SUN RES -- TYPE CMH FT1 -- {MM/DD/YY} {HH:MM}

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

Table 1 – Physical and Electrical Data

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insulation Color	Insul. Thickness	Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C	Inductive Rectance	Min Bending Radius	Jacket Color
	AWG	No.	strands	inch		mil	mil	inch	lb / 1000ft	lb / 1000ft	Ω /1000ft	Ω /1000ft	Ω/1000ft	inch	
18 AWG															
55306◊	18	6	SOLID	0.04	RD,WE,GN,BE,YW,BN	5	15	0.186	29	37	6.659	8.265	0.036	0.74	BN

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item
TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Copyright © 2026 Southwire Company, LLC. All Rights Reserved