# MC-PCS Duo™ Power & Control/Signal Cable GSIA

Copper THHN/THWN Insulated Singles. UL Listed 600 Volts. Rated VW-1. Galvanized Steel Interlocked Armor. Signal: 16 AWG Copper TFN insulated singles.





Image not to scale. See Table 1 for dimensions.

## CONSTRUCTION:

1. **Conductor:** Solid copper per ASTM B3
2. **Insulation:** Polyvinyl Chloride with Nylon Sheath Type THHN/THWN
3. **Ground:** Green Polyvinyl Chloride with Nylon Sheath Type THHN/THWN insulated ground conductor
4. **Signal:** 16 AWG copper Type TFN insulated singles (pink and purple). Overall light blue jacket over the signal cables
5. **Binder:** Mylar tape
6. **Armor:** Galvanized Steel Interlocked Armor

## APPLICATIONS AND FEATURES:

**Southwire MC PCS Duo™ Power & Control/Signal Galvanized Steel Armor cable is suitable for use as follows:**

- Branch, feeder and service power distribution in commercial, industrial, institutional, and multi-residential buildings
- Fished or embedded in plaster
- Concealed or exposed installations
- LED lighting with 0-10V dimming
- Environmental air-handling spaces per NEC 300.22 (C)
- Places of Assembly per NEC 518.4 and theaters per NEC 520.5
- Installation in cable tray and approved raceways
- Under raised floors for information technology equipment conductors and cables per NEC 645
- Class I Div. 2, Class II Div 2, & Class III Div. 1 Hazardous Locations
- Binder tape with print legend wrapped around assembly
- Type THHN/THWN rated 90ºC dry
- Unjacketed Type MC cables are rated for dry, indoor locations only per NEC 330.10(A)(10)
- Anti-Short bushing not required

**Southwire MC PCS Duo™ Type MC Cable meets or exceeds the following requirements:**

- UL Online Product Guide Info - Metal-Clad Cable (PJAZ) ( www.ul.com )
- Federal Specification A-A59544 (formerly J-C-30B)
- NFPA 70 (National Electrical Code), Article 330
- Listed for use in UL 1, 2 and 3 Hour Through Penetration Firestop Systems

## SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire


Copyright © 2026 Southwire Company, LLC. All Rights Reserved

- UL 83 Thermoplastic Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1479 Standard for Safety Fire Tests of Penetration Firestops
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- Buy American: Compliant with Buy American Requirements, found in 49 U.S.C. § 5323(j); specify "Made in the USA Only!" when ordering to ensure your project receives American made products.

## SAMPLE PRINT LEGEND:

SOUTHWIRE E96627 {UL} TYPE MC XX AWG THHN OR THWN CDRS FOR USE IN CABLE TRAYS 600 VOLTS - STL

### Table 1 – Weights and Measurements

| Stock Number | Cond. Size | Conductor Number | Color | Diameter Over Conductor | Conductor Stranding | Insulation Thickness | Ground Size | Diameter Over Armor | Copper Weight | Overall Weight |
|---|---|---|---|---|---|---|---|---|---|---|
| | AWG/ Kcmil | | | inch | | mils | No. x AWG | inch | lbs/1000ft | lbs/1000ft |
| 12 AWG \| SOLID Strands | | | | | | | | | | |
| 599396 | 12 | 2 | BK,WE | 0.081 | SOLID | 15 | 1x12 | 0.611 | 76 | 219 |

All dimensions are nominal and subject to normal manufacturing tolerances
◊ Cable marked with this symbol is a standard stock item

### Table 2 – Electrical and Engineering Data

| Cond. Size | Conductor Number | Min. Bend Radius | DC Resistance at 25°C | AC Resistance at 75°C | Inductive Reactance @ 60Hz | Allowable Ampacity Raceway 75°C | Allowable Ampacity Raceway 90°C |
|---|---|---|---|---|---|---|---|
| AWG/ Kcmil | | Inches | Ω/1000ft | Ω/1000ft | Ω/1000ft | Amp | Amp |
| 12 AWG \| SOLID Strands | | | | | | | |
| 12 | 2 | 4.3 | 1.662 | 2.063 | 0.054 | 25 | 30 |

***** Ampacities based upon 2023 NEC Table 310.16 and do not take into account the overcurrent protection limitations in NEC 240.4(D) of 15 Amps for 14 AWG CU, 20 Amps for 12 AWG CU, and 30 Amps for 10 AWG CU (independent of the conductor temperature rating and stranding if size is present in table). Also, see NEC sections 310.15 and 110.14(C) for additional requirements.
***** Ampacities have been adjusted for more than Three Current-Carrying Conductors.


Copyright © 2026 Southwire Company, LLC. All Rights Reserved