



## Flexible Hook-Up Wire/Appliance Wire Styles 3499

150°C 7500 Volts. Flexible Stranded Tinned Copper Conductor. EPDM Insulation.




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Flexible stranded tinned copper. Bare copper available upon request
2. **Conductor Separator:** Mylar
3. **Insulation:** Black, Ethylene Propylene Diene Monomer (EPDM)

### APPLICATIONS AND FEATURES:

Designed for Internal Wiring Appliances, where no flexing occurs, either after installation or during servicing.

- AWM Style 3499: 150°C/7500V

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B173 Rope-Lay-Stranded Copper Conductors Having Concentric-Stranded Members
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 758 Standard for Appliance Wiring Material

### SAMPLE PRINT LEGEND:

XX AWG (XX.XXmm<sup>2</sup>) E57498 MASTER-DESIGN (RU) AWM 3499 150C 7500V -- MADE IN USA





**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C
	AWG	No.	strands	inch	mil	inch	lb /1000ft	Ω /1000ft	Ω /1000ft
AWM									
F2T034	2/0	1	1330	0.409	130	0.675	544	0.087	0.104

All dimensions are nominal and subject to normal manufacturing tolerances  
◊ Cable marked with this symbol is a standard stock item



Ampacity

