

## Flexible Hook-Up Wire/Appliance Wire Styles 3499

150°C 7500 Volts. Flexible Stranded Tinned Copper Conductor. EPDM Insulation.




Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

- Conductor:** Flexible stranded tinned copper. Bare copper available upon request
- Conductor Separator:** Mylar
- Insulation:** Black, Ethylene Propylene Diene Monomer (EPDM)

### APPLICATIONS AND FEATURES:

Designed for Internal Wiring Appliances, where no flexing occurs, either after installation or during servicing.

- AWM Style 3499: 150°C/7500V

### SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B33 Standard Specification for Tin-Coated Soft or Annealed Copper Wire
- ASTM B173 Rope-Lay-Stranded Copper Conductors Having Concentric-Stranded Members
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- UL 758 Standard for Appliance Wiring Material

### SAMPLE PRINT LEGEND:

XX AWG (XX.XXmm<sup>2</sup>) E57498 MASTER-DESIGN (RU) AWM 3499 150C 7500V -- MADE IN USA



**Table 1 – Physical and Electrical Data**

Stock Number	Cond. Size	Cond. Number	Cond. Strands	Diameter Over Cond.	Insul. Thickness	Approx. OD	Approx. Weight	DC Resistance @ 25°C	AC Resistance @ 75°C
	AWG	No.	strands	inch	mil	inch	lb /1000ft	Ω /1000ft	Ω /1000ft
AWM									
F3T026	3/0	1	1672	0.460	125	0.740	663	0.069	0.083

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

Ampacity



**Southwire Company, LLC | One Southwire Drive, Carrollton, GA 30119 | [www.southwire.com](http://www.southwire.com)**

Copyright © 2026 Southwire Company, LLC. All Rights Reserved

UPDATED: June 23, 2025, 11:44 a.m. UTC REVISION: 1.000.005

