

CSA TECK 90 CU 3/C 5000V NON-SHIELDED TRXLPE POWER CABLE

5000V, Non-Shielded, TRXLPE Insulated, FT4, -40°C, HL (Hazardous Locations), AG14 & 90°C




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class B stranded copper, compressed or compact, in accordance with ASTM B3 and B8.
2. **Conductor Shield:** Extruded semi-conducting thermosetting polymeric layer
3. **Insulation:** TRXLPE (cross-linked polyethylene), Thickness: 0.090" (2.3 mm) - nominal, 90°C
4. **Grounding Conductor:** Class B compressed or compact stranded bare copper, in accordance with ASTM B3 and B8
5. **Binder:** Polypropylene tape
6. **Inner Jacket:** Black PVC, Thickness: No. 2 AWG to No. 3/0 AWG = 0.080" (2.0 mm); No. 4/0 AWG to 500 kcmil = 0.110" (2.8 mm); 750 kcmil to 1000 kcmil = 0.140" (3.6 mm)
7. **Aarmor:** Aluminum Interlocked Armour (AIA)
8. **Overall Jacket:** Orange PVC (optional colours available), Thickness: No. 2 AWG to 250 kcmil = 0.060" (1.5 mm); 350 kcmil to 750 kcmil = 0.075" (1.9 mm); 1000 kcmil = 0.090" (2.3 mm)

APPLICATIONS AND FEATURES:

Southwire's Teck 90, 5000V, non-shielded, TRXLPE insulated (treeing resistant) power cable is a CSA approved armoured cable for industrial and commercial medium voltage applications. FT4, -40°C, HL, AG14 and 90°C rated for use in harsh Canadian environments. Rated for installation in cable trays, duct banks, direct burial, troughs, hazardous locations, continuous rigid cable supports, and is concrete encaseable.

- -40°C - CSA Cold Bend and Impact Temperature
- -25°C - Min. Installation Temperature
- 90°C - Max. Continuous Operating Temperature
- 140°C for Emergency Overload Temperature
- 250°C for Short Circuit Temperature

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- CSA C22.2 No. 174 Cables in Hazardous Locations
- CSA C22.2 No. 131 Type TECK 90 Cable
- CSA C22.2 No. 2556 & No. 0.3 Wire and Cable Test Methods
- CSA LTGG [-40°C] - as per C68.10 - for Cold Bend and Impact rating
- CSA HL - for Hazardous Locations rating





- CSA SUN RES - for Sunlight Resistant rating
- CSA AG14 - Acid Gas Compliance
- ICEA S-96-659 (NEMA WC 71) 2001-5000 V Nonshielded Cables
- IEEE 383 Flame Test (70,000 btu)
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- FT1 Flame Test (1,706 BTU/Hr nominal - Vertical Wire Flame Test)

SAMPLE PRINT LEGEND:

SOUTHWIRE {CSA} LL90458 3/C XX KCMIL CU TECK 90 TRXLPE CDRS WITH GROUND -40°C FT4 SUN. RES. AG14 5000V
HL {YYYY} USA {SEQUENTIAL METER MARKS}

Table 1 – Weights and Measurements

Cond. Size	Strand	Diameter Over Conductor	Insul. Thickness	Ground	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
AWG/Kcmil	No.	inch	mil	No. x AWG	mil	inch	mil	inch	lb/1000ft	lb/1000ft
1	19	0.322	90	1x6	85	1.682	55	1.792	864	1788

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Other conductor sizes and outer jacket colours are available upon request. (#s in brackets represent # of strands / conductor. Number of strands may vary as per CSA standard.)

** Black Jacket

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Air 90°C
AWG/Kcmil	inch	lb	Ω/1000ft	Ω/1000ft	Ω/1000ft	Amp
1	12.5	2008	0.128	0.154	0.034	197

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

Table 3 – Weights and Measurements (Metric)

Cond. Size	Strand	Diameter Over Conductor	Insul. Thickness	Ground	Inner Jacket Thickness	Dia. Over Armour	Overall Jacket Thickness	Approx. OD	Copper Weight	Approx. Weight
AWG/Kcmil	No.	mm	mm	No. x AWG	mm	mm	mm	mm	kg/km	kg/km
1	19	8.18	2.29	1x6	2.16	42.72	1.40	45.52	1286	2661

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Other conductor sizes and outer jacket colours are available upon request. (#s in brackets represent # of strands / conductor. Number of strands may vary as per CSA standard.)

** Black Jacket

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.





Table 4 – Electrical and Engineering Data (Metric)

Cond. Size	Min Bending Radius	Max Pull Tension	DC Resistance @ 25°C	AC Resistance @ 90°C	Inductive Reactance @ 60Hz	Allowable Ampacity In Air 90°C
AWG/ Kcmil	mm	newton	Ω/km	Ω/km	Ω/km	Amp
1	317.50	8936	0.4199	0.51	0.1115	197

* Inductive impedance is based on non-ferrous conduit with one diameter spacing center-to-center.

