



CU 600/1000V XLPE Insulation ARMOR-X® Thermoplastic LSZH-TP Jacket XHHW-2. CT Rated -Sunlight Resistant - For Direct Burial - Silicone Free

Type MC-HL Power Cable 600 or 1000 Volt Four Copper Conductors, Cross Linked Polyethylene (XLPE) Insulation Type XHHW-2, Continuous Corrugated Welded Armor - ARMOR-X®, Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP) Jacket with 1 Bare Copper Ground




Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

- Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8
- Insulation:** Cross Linked Polyethylene (XLPE) Type XHHW-2
- Grounding Conductor:** Class B compressed stranded bare copper per ASTM B3 and B8
- Filler:** Paper filler (cable size 8 & 6 uses polypropylene filler)
- Binder:** Polypropylene tape
- Armor:** ARMOR-X® Continuous Corrugated Welded armor
- Overall Jacket:** Thermoplastic SOLONON® Low Smoke Zero Halogen (LSZH-TP)

APPLICATIONS AND FEATURES:

Southwire's 600 Volt Type MC-HL ARMOR-X® power cables are suited for use in wet and dry areas, conduits, ducts, troughs, trays, direct burial, aerial supported by a messenger, and where superior electrical properties are desired. These cables are capable of operating continuously at the conductor temperature not in excess of 90°C for normal operation in wet and dry locations, 130°C for emergency overload, 250°C for short circuit conditions, and -40°C for cold bend. For uses in Class I, II, and III, Division 1 and 2 hazardous locations per NEC Article 501, 502, and 503.

SPECIFICATIONS:





- ASTM B3 Soft or Annealed Copper Wire
- ASTM B8 Concentric-Lay-Stranded Copper Conductors
- UL 44 Thermoset-Insulated Wires and Cables
- UL 1569 Metal-Clad Cables
- UL 1685 FT4 Vertical-Tray Fire Propagation and Smoke Release Test
- UL 2225 Cables and Cable-Fittings For Use In Hazardous (Classified) Locations
- ICEA S-58-679 Cable Conductor Identification Method 3 (1-BLACK, 2-RED, 3-BLUE)
- ICEA S-95-658 (NEMA WC70) Power Cables Rated 2000 Volts or Less for the Distribution of Electrical Energy
- IEEE 1202 FT4 Flame Test (70,000) BTU/hr Vertical Tray Test
- NFPA 130 Standard for Fixed Guideway Transit and Passenger Rail Systems (500kcmil & Larger)

SAMPLE PRINT LEGEND:

{SQFTG_DUAL} SOUTHWIRE® {UL} ARMOR-X TYPE MC-HL 4/C XX AWG or KCMIL (XX.X{MM2}) CU XHHW-2 GW 1 X XX AWG 90°C SOLONON® JACKET -40°C ST1 SUN.RES. DIR. BUR. FOR CT USE 600V/1kV IEEE1202/FT4 -- {NOM}-ANCE Tipo MC XHHW-2 CT FT4

Table 1 – Weights and Measurements

| Cond. Size | Cond. Number | Strand Count | Diameter Over Conductor | Insul. Thickness | Ground | Dia. Over Armor | Jacket Thickness | Approx. OD | Copper Weight | Approx. Weight | Jacket Color |
|------------|--------------|----------------|-------------------------|------------------|-----------|-----------------|------------------|------------|---------------|----------------|--------------|
| AWG/Kcmil | | No. of Strands | inch | mil | No. x AWG | inch | mil | inch | lb/1000ft | lb/1000ft | |
| 3/0 | 4 | 19 | 0.405 | 60 | 1 x 4 | 1.670 | 55 | 1.796 | 2223 | 2961 | Black |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

TBA stock codes are estimations only and actual product may vary. Please wait until a stock code is assigned to purchase connectors and/or fittings.

Table 2 – Electrical and Engineering Data

| Cond. Size | Cond. Number | Min Bending Radius | Max Pull Tension | DC Resistance @ 25°C | AC Resistance @ 75°C | Capacitive Reactance @ 60Hz | Inductive Reactance @ 60Hz | Allowable Ampacity At 75°C | Allowable Ampacity At 90°C |
|------------|--------------|--------------------|------------------|----------------------|----------------------|-----------------------------|----------------------------|----------------------------|----------------------------|
| AWG/Kcmil | | inch | lb | Ω/1000ft | Ω/1000ft | MΩ*1000ft | Ω/1000ft | Amp | Amp |
| 3/0 | 4 | 12.3 | 4295 | 0.064 | 0.078 | 0.014 | 0.042 | 160 | 180 |

* Ampacities based upon 2023 NEC Table 310.16. See NEC sections 310.15 and 110.14(C) for additional requirements.

* Ampacities have been adjusted for more than Three Current-Carrying Conductors.

