



## 600V ROYAL® SOOW Cord Control with Black Jacket 90°C. MSHA Approved

600 Volt 90°C Flexible Cord. Heat, Moisture and Oil Resistant EPDM Rubber Insulation, Heat, Moisture and Oil Resistant Flexible CPE Jacket



Image not to scale. See Table 1 for dimensions.

### CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant EPDM
3. **Filler:** Waxed paper fillers, with a tissue-paper separator wrapped around the assembly
4. **Jacket:** Black CPE (Other colors available upon request)

### APPLICATIONS AND FEATURES:

Southwire Type SOOW Flexible Cords UL/ CSA listed are permitted for use as specified by Article 400 and related articles of the 2014 National Electrical Code. The cable is rated -40°C to 90°C, water, oil, and weather resistant. Southwire Type SOOW Flexible Cords are designed for extra hard usage on industrial equipment, heavy tools, battery chargers, portable lights, welding leads, marine dockside power, power extensions and mining applications.

### SPECIFICATIONS:

- UL 62 Flexible Cords and Cables
- CSA C22.2 No. 49 Flexible Cords and Cables
- MSHA flame test - P07-KA070018-1MSHA
- Passes CSA FT2 Flame Test
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- NEC Article 501.140 Class I Division 2
- Federal Specification J-C-580B

### SAMPLE PRINT LEGEND:

SOUTHWIRE® ROYAL® CORD XX/C XX AWG ({mm<sup>2</sup>}) SOOW E46194 {UL} 600V -40°C TO 90°C -- {CSA} LL90458 SOOW 600V -40°C TO 90°C FT2 WATER RESISTANT {NOM}-ANCE -- {MSHA}

### PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.





**Table 1 – Weights and Measurements**

Stock Number	AWG/Kcmil
558150 7	4/0

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

**Table 2 – Weights and Measurements (Metric)**

Stock Number	AWG/Kcmil
558150 7	4/0

\* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.





**Color Table**

Stock Number	Installation Color	
558034	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	None/Pap
558037	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	None/Pap
558302	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	None/Pap
558039	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe	None/Pap
558041	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe	None/Pap
558043	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe	None/Pap
558052	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe, OE-WE 2xStripe, BE-WE 2xStripe, WE-BK 2xStripe, RD-BK 2xStripe, GN-BK 2xStripe, OE-BK 2xStripe	None/Pap
558526	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Pap
558527	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	Paper/Pap
558305	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	Paper/Pap
558028	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe	None/Pap
558018	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe	None/Pap
558016	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe	None/Pap
558026	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe, BE-RD 1xStripe, BK-WE 2xStripe, RD-WE 2xStripe, GN-WE 2xStripe, OE-WE 2xStripe, BE-WE 2xStripe, WE-BK 2xStripe, RD-BK 2xStripe, GN-BK 2xStripe, OE-BK 2xStripe	Paper/My
558094	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Pap
558270	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe	Paper/Pap
558995	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	Paper/Pap
558097	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe	Paper/Str
558139	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe	None/Pap
558981	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Pap
558982	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	None/Pap
558307	W, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe	Paper/Pap





Stock Number	Conductor Color	Material
558150	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe, RD-BK 1xStripe, GN-BK 1xStripe, OE-BK 1xStripe, BE-BK 1xStripe, BK-RD 1xStripe, WE-RD 1xStripe, GN-RD 1xStripe, OE-RD 1xStripe	Poly/Paper
558151	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe	Paper/Paper
558152	BK, WE, RD, GN, OE, BE, BK-WE 1xStripe, RD-WE 1xStripe, GN-WE 1xStripe, OE-WE 1xStripe, BE-WE 1xStripe, WE-BK 1xStripe	None/Paper

