



600V ROYAL® S00W Power Cord Non-UL/CSA with Black Jacket 90°C. MSHA Approved

600 Volt, 90°C Flexible Cord. Heat, Moisture and Oil Resistant EPDM Rubber Insulation and Heat, Moisture and Oil Resistant Flexible CPE Jacket, Non UL / Non CSA.



Image not to scale. See Table 1 for dimensions.

CONSTRUCTION:

1. **Conductor:** Class K stranded bare copper per ASTM B-174
2. **Insulation:** Heat, moisture and oil resistant EPDM
3. **Filler:** Waxed paper fillers
4. **Jacket:** Black CPE (Other colors available upon request)

APPLICATIONS AND FEATURES:

Southwire Royal® Non UL/Non CSA S00W cord is designed for use with industrial equipment, heavy tools, battery chargers, portable lights and power extensions, suitable for outdoor applications. The cable is rated -40°C to 90°C, sunlight, water, oil, and weather resistant. Southwire Type S00W Flexible Cords are permitted for use as specified by Article 400 and related articles of the 2014 National Electrical Code.

SPECIFICATIONS:

- ASTM B3 Soft or Annealed Copper Wire
- ASTM B174 Standard Specification for Bunch-Stranded Copper
- MSHA flame test - P07-KA070018-1MSHA
- RoHS-3 Complies with European Directive 2015/863
- NEC Article 400 Flexible Cords, Cables and Fixture Wire
- Federal Specification J-C-580B

SAMPLE PRINT LEGEND:

SOUTHWIRE® ROYAL® CORD X/C X AWG (X.XXmm²) S00W 600V -40C TO 90C

PACKAGING:

Standard lengths: 250', 500' and 1,000' reels. Other lengths available upon request.





Table 1 – Weights and Measurements

| Stock Number | CCI Part # | Cond. Size | Cond. Number | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Ampacity | Insul. Color | Jacket Color |
|--------------|------------|------------|--------------|---------------|------------------|------------------|------------|----------------|----------|----------------|--------------|
| | | AWG/Kcmil | No. | No. | mil | mil | inch | lb/1000ft | Amp | | |
| 558105 | 822470 | 8 | 5 | 133 | 45 | 105 | 0.834 | 492 | 28 | BK,WE,RD,GN,OE | BK |

All dimensions are nominal and subject to normal manufacturing tolerances

◊ Cable marked with this symbol is a standard stock item

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Table 2 – Weights and Measurements (Metric)

| Stock Number | CCI Part # | Cond. Size | Cond. Number | Cond. Strands | Insul. Thickness | Jacket Thickness | Approx. OD | Approx. Weight | Ampacity * | Insul. Color | Jacket Color |
|--------------|------------|------------|--------------|---------------|------------------|------------------|------------|----------------|------------|----------------|--------------|
| | | AWG/Kcmil | No. | No. | mm | mm | mm | kg/km | Amp | | |
| 558105 | 822470 | 8 | 5 | 133 | 1.14 | 2.67 | 21.18 | 732 | 28 | BK,WE,RD,GN,OE | BK |

* Ampacities are based on TABLE 400.5(A)(1) of the 2023 National Electrical Code and CEC Table 12.

Color Code

| # of Conductor | Color Sequence |
|----------------|----------------------------------|
| 2 | Black, White |
| 3 | Black, White, Green |
| 4 | Black, White, Red, Green |
| 5 | Black, White, Red, Green, Orange |

